

SF-BIT-SL 0,5X3,0-70 - Screw insert



1212567

<https://www.phoenixcontact.com/us/products/1212567>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Screw bit, bladed, E6.3-1/4" drive, size: 0.5 x 3.0 x 70 mm, hardened, suitable for holder according to DIN 3126-F6.3/ISO 1173

Your advantages

- Tools for SF-ASD 21 cordless screwdriver in various versions

Commercial data

Item number	1212567
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3149
GTIN	4046356590020
Weight per piece (including packing)	8.85 g
Weight per piece (excluding packing)	8.85 g
Customs tariff number	82079030
Country of origin	CZ

SF-BIT-SL 0,5X3,0-70 - Screw insert



1212567

<https://www.phoenixcontact.com/us/products/1212567>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type

Screwdriver tools

Type

Bladed

Connection data

Output

Bladed

Dimensions

Blade width

3 mm

Blade height

70 mm

Length

70 mm

Blade thickness

0.5 mm

Material specifications

Color

silver-colored

Material

Steel

Standards and regulations

Tests

DIN 3126 drive, output 3127-1

SF-BIT-SL 0,5X3,0-70 - Screw insert



1212567

<https://www.phoenixcontact.com/us/products/1212567>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212567>



EAC

Approval ID: RU C-DE.AI30.B.01750

SF-BIT-SL 0,5X3,0-70 - Screw insert



1212567

<https://www.phoenixcontact.com/us/products/1212567>

Classifications

ECLASS

ECLASS-13.0	21044204
ECLASS-15.0	21044204

ETIM

ETIM 9.0	EC003864
----------	----------

UNSPSC

UNSPSC 21.0	27112800
-------------	----------

SF-BIT-SL 0,5X3,0-70 - Screw insert



1212567
<https://www.phoenixcontact.com/us/products/1212567>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com