

RC-17S1N8E0000 - Contact insert

1602284

<https://www.phoenixcontact.com/us/products/1602284>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, M23, number of positions: 17, contact connection type: Socket, Crimp connection, series: NC, RC, RM, TU, UC

Commercial data

Item number	1602284
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAFU
GTIN	4046356238953
Weight per piece (including packing)	10.9 g
Weight per piece (excluding packing)	5.78 g
Customs tariff number	85389099
Country of origin	DE

RC-17S1N8E0000 - Contact insert



1602284

<https://www.phoenixcontact.com/us/products/1602284>

Technical data

Product properties

Product type	Contact insert
Series	NC
	RC
	RM
	TU
	UC
Application	Signal
Number of positions	17
Connection profile	17
Coding	N
Thread type	M23

Electrical properties

Contact: Contact group 1

Contact diameter	1 mm
Min. cross section	0.22 mm ²
Max. cross section	0.56 mm ²
Nominal current I _N	8 A (for max. connection cross section)
Nominal voltage U _N	48 V AC
	74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Connection method	Crimp connection
-------------------	------------------

Material specifications

Material Insulating body	PA 6.6
Material Contact	CuZn
Material Contact surface	Ni/Au

Connector

Direction of rotation	Standard
-----------------------	----------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	50
-----------------------------	----

Environmental and real-life conditions

RC-17S1N8E0000 - Contact insert



1602284

<https://www.phoenixcontact.com/us/products/1602284>

Ambient conditions

Permissible humidity (storage/transport)	50 % ... 65 %
--	---------------

RC-17S1N8E0000 - Contact insert


1602284

<https://www.phoenixcontact.com/us/products/1602284>



Drawings

Schematic diagram



Connector pin assignment

RC-17S1N8E0000 - Contact insert



1602284

<https://www.phoenixcontact.com/us/products/1602284>

Classifications

ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

ETIM

ETIM 9.0	EC003557
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RC-17S1N8E0000 - Contact insert



1602284

<https://www.phoenixcontact.com/us/products/1602284>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com