

RC-Z2391 - Cable clamp type cage and shield adapter



1604449

<https://www.phoenixcontact.com/us/products/1604449>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable clamp type cage and shield adapter, shielded: yes, litz wire bundle diameter: 4.9 mm, cable diameter range: 7.5 mm ... 9.5 mm, series: NC, RC

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1604449 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | AB31 |
| Product key | ABRAFU |
| GTIN | 4046356249409 |
| Weight per piece (including packing) | 7.6 g |
| Weight per piece (excluding packing) | 6.5 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

RC-Z2391 - Cable clamp type cage and shield adapter



1604449

<https://www.phoenixcontact.com/us/products/1604449>

Technical data

Product properties

| | |
|------------------------------|-----------------------|
| Product type | Cable clamp type cage |
| Series | NC |
| | RC |
| Type of the screw connection | EMC |
| Shielded | yes |

Cable/line

| | |
|-------------------------|-------------------|
| External cable diameter | 7.5 mm ... 9.5 mm |
|-------------------------|-------------------|

Mechanical properties

Mechanical data

| | |
|------------------------------|-----|
| Type of the screw connection | EMC |
|------------------------------|-----|

RC-Z2391 - Cable clamp type cage and shield adapter



1604449

<https://www.phoenixcontact.com/us/products/1604449>

Classifications

ETIM

| | |
|----------|----------|
| ETIM 8.0 | EC000441 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121300 |
|-------------|----------|

RC-Z2391 - Cable clamp type cage and shield adapter



1604449

<https://www.phoenixcontact.com/us/products/1604449>

Environmental product compliance

| | |
|---|---|
| EU RoHS | |
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |
| China RoHS | |
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |
| EU REACH SVHC | |
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com