

VS-TO-OW-2-F-9010 - Terminal outlet



1653003

<https://www.phoenixcontact.com/us/products/1653003>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Terminal outlet, surface mounting, IP20, two slots for contact inserts with the Freenet system



Your advantages

- Panel mounting
- Can be optionally equipped with copper and FO inserts
- Halogen free, according to DIN VDE 0472/815

Commercial data

Item number	1653003
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB15
Product key	ABNGCB
GTIN	4017918969974
Weight per piece (including packing)	115.1 g
Weight per piece (excluding packing)	115.1 g
Customs tariff number	85366990
Country of origin	CH

VS-TO-OW-2-F-9010 - Terminal outlet



1653003


<https://www.phoenixcontact.com/us/products/1653003>

Technical data

Product properties

Product type	Network distributor box
Application	Einbauplätze für Kontakteinsätze mit Freenet-System
No. of cable outlets	2
Number of module slots	2
Number of slots	2

Dimensions

Dimensional drawing	
Width	80 mm
Length	80 mm

Material specifications

Color	pure white RAL 9010
Flammability rating according to UL 94	HB
Housing material	PC+ABS

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	5 °C ... 55 °C

Mounting

Mounting type	Surface/Panel mounting
---------------	------------------------

VS-TO-OW-2-F-9010 - Terminal outlet


1653003

<https://www.phoenixcontact.com/us/products/1653003>



Drawings

Dimensional drawing



Terminal outlet

VS-TO-OW-2-F-9010 - Terminal outlet



1653003

<https://www.phoenixcontact.com/us/products/1653003>

Classifications

ETIM

ETIM 8.0	EC002597
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

VS-TO-OW-2-F-9010 - Terminal outlet



1653003

<https://www.phoenixcontact.com/us/products/1653003>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com