

SAC-4P-M12MS/ 4,0-PVC/M12FR - Sensor/actuator cable

1447196
<https://www.phoenixcontact.com/us/products/1447196>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-pos., PVC, RAL 7021 (black-gray), straight M12 male plug, A-coded, to angled M12 female plug, A-coded, cable length: 4.0 m

Commercial data

Item number	1447196
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	AF1CCA
GTIN	4046356661379
Weight per piece (including packing)	156 g
Weight per piece (excluding packing)	137.772 g
Country of origin	DE

SAC-4P-M12MS/ 4,0-PVC/M12FR - Sensor/actuator cable



1447196

<https://www.phoenixcontact.com/us/products/1447196>

Technical data

Product properties

Product type	Sensor/actuator cable
--------------	-----------------------

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Electrical properties

Nominal voltage U_N	250 V AC
	250 V DC
Nominal current I_N	4 A

Connection data

Conductor connection

Tightening torque	0.4 Nm
-------------------	--------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67

SAC-4P-M12MS/ 4,0-PVC/M12FR - Sensor/actuator cable



1447196

<https://www.phoenixcontact.com/us/products/1447196>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-4P-M12MS/ 4,0-PVC/M12FR - Sensor/actuator cable



1447196

<https://www.phoenixcontact.com/us/products/1447196>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com