

SACC-AT04-6P-RS-IV - Connector housing



1520954

<https://www.phoenixcontact.com/us/products/1520954>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Commercial data

Item number	1520954
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BF72
Product key	AF2IEA
GTIN	4063151984595
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	8.7 g
Country of origin	MX

SACC-AT04-6P-RS-IV - Connector housing



1520954

<https://www.phoenixcontact.com/us/products/1520954>

Technical data

Notes

General	AT04-6P-RD01BLK
General	Use with Size 16 pin contacts

Product properties

Product type	Contact insert
Series	AT04
Contact numbering	1 - 6
Shielded	no


Electrical properties

Specific dielectric strength	1500 V AC (Less than 2 mA current leakage)
Insulation resistance	1000 MΩ (at 25 °C)
Nominal voltage U_N	50 V AC/DC (IEC rating)
Nominal current I_N	13 A (MAX)

Connection data

Connection method	Crimp contacts
-------------------	----------------

Dimensions

Dimensional drawing	
Width	21.1 mm
Height	24.3 mm
Length	46.2 mm

Material specifications

Seal material Profile gasket	Silicon
Seal material Cable seal	Silicon
Housing material	PA-GF

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

Characteristics

Specific dielectric strength	1500 V AC (Less than 2 mA current leakage)
------------------------------	--

SACC-AT04-6P-RS-IV - Connector housing



1520954

<https://www.phoenixcontact.com/us/products/1520954>

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP68 (in mated condition)
	IP69K (in mated condition)
Ambient temperature (operation)	-55 °C ... 125 °C


SACC-AT04-6P-RS-IV - Connector housing

1520954

<https://www.phoenixcontact.com/us/products/1520954>


Drawings

Dimensional drawing



AT04-6P top view and side view

Schematic diagram



AT04-6P pin assignment

SACC-AT04-6P-RS-IV - Connector housing



1520954

<https://www.phoenixcontact.com/us/products/1520954>

Classifications

ECLASS

ECLASS-15.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

SACC-AT04-6P-RS-IV - Connector housing



1520954

<https://www.phoenixcontact.com/us/products/1520954>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com