

ME PLC 40 MT S BK - Insertion plate



2201496

<https://www.phoenixcontact.com/us/products/2201496>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Matrix with defined engagement mechanism, for assembly underneath the cover in short design,
color: black



Your advantages

- Easy, tool-free mounting

Commercial data

Item number	2201496
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC15
Product key	ACHEAZ
GTIN	4046356838641
Weight per piece (including packing)	3.69 g
Weight per piece (excluding packing)	3 g
Customs tariff number	85389099
Country of origin	DE

ME PLC 40 MT S BK - Insertion plate

2201496

<https://www.phoenixcontact.com/us/products/2201496>



Technical data

Notes

Assembly note	Please observe the application note in the download area.
---------------	---

Product properties

Product type	Cover
Housing type	DIN rail housing
Housing series	ME PLC
Ventilation openings present	no

Dimensions

Width	35.27 mm
Height	47.37 mm
Depth	8.7 mm

Material specifications

Color (Insertion plate)	black (RAL 9005)
Material Housing	PC
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions	
Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	95 %

Mounting

Mounting type	Clip mounting
---------------	---------------

Packaging specifications

Type of packaging	packed in cardboard
Outer packaging type	Carton

ME PLC 40 MT S BK - Insertion plate

2201496

<https://www.phoenixcontact.com/us/products/2201496>



Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

ME PLC 40 MT S BK - Insertion plate

2201496

<https://www.phoenixcontact.com/us/products/2201496>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com