

D L 5,7 QVGA P - Display


2203549

<https://www.phoenixcontact.com/us/products/2203549>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Graphic LCD module, 5.7", 320 x 240 pixels, FSTN transmissive/negative 12:00, LED backlight, interface: parallel, operating temperature: -20 °C ... 70 °C



Your advantages

- Graphic LCD module
- Easy and time-saving integration into DCS series electronics housings
- Long-term availability
- Ideal protective shield and gasket material
- Backlighting can be switched on and off
- Common interface for your electronics

Commercial data

Item number	2203549
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC05
Product key	ACGAAA
GTIN	4055626481999
Weight per piece (including packing)	171.4 g
Weight per piece (excluding packing)	171.4 g
Customs tariff number	85312095
Country of origin	TW

D L 5,7 QVGA P - Display

2203549

<https://www.phoenixcontact.com/us/products/2203549>



Technical data

Product properties

Product type	Display
Display	
Display type	Graphic LCD module
Display type	LCD with backlighting
Display type	transmissive
Panel technology	FSTN
Diagonals (cm)	14.48 cm
Diagonals (inch)	5.7 in.
Screen resolution	320 x 240 Pixel(s) (QVGA)
Display formats	4:3
Display lighting type	LED
Service life, lighting appliance	40000 h
Viewing direction	6:00
Controller	NT7701
Representation	negative

Interfaces

Interface	parallel
-----------	----------

Dimensions

Dimensions	143 mm x 103 mm x 9 mm (Mounting panel dimensions)
	120 mm x 90 mm (Viewing area)
	115 mm x 86 mm (Active range)

Material specifications

Surface characteristics	untreated
-------------------------	-----------

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (storage/transport)	-30 °C ... 80 °C

Mounting

Mounting type	Screw mounting
---------------	----------------

Packaging specifications

Type of packaging	packed in cardboard
-------------------	---------------------

D L 5,7 QVGA P - Display

2203549

<https://www.phoenixcontact.com/us/products/2203549>



Classifications

ECLASS

ECLASS-13.0	27261890
-------------	----------

ETIM

ETIM 9.0	EC011541
----------	----------

UNSPSC

UNSPSC 21.0	43211900
-------------	----------

D L 5,7 QVGA P - Display

2203549
<https://www.phoenixcontact.com/us/products/2203549>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com