

PSD-S ME OB/MB - Mounting material



2700155

<https://www.phoenixcontact.com/us/products/2700155>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Outlet box with magnetic base for base mounting, black



Your advantages

- Magnetic base for tool-free mounting on metal surfaces
- With concealed cable routing

Commercial data

Item number	2700155
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR07
Product key	DRL117
GTIN	4046356491464
Weight per piece (including packing)	318.5 g
Weight per piece (excluding packing)	290 g
Customs tariff number	39269097
Country of origin	DE

PSD-S ME OB/MB - Mounting material



2700155

<https://www.phoenixcontact.com/us/products/2700155>

Technical data

Notes

Note on application

General	Only for industrial use
Recommendation	Suitable pan head screw for plastics 4 x 20 mm


Product properties

Product type	Assembly element
Product family	PSD-S
Scope of supply	2 x plastic screw 1 x cable threaded joint 1 x nut 1 x seal
	2 x plastic screw 1 x cable threaded joint 1 x nut 1 x seal

Connection data

Connection method	Screw connection
-------------------	------------------

Dimensions

Dimensional drawing	
Height	45.5 mm
Diameter	70 mm

Material specifications

Color	black
Material	PA-GF

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-30 °C ... 60 °C

Mounting

Mounting type	Base mounting (Magnetic holder)
	Tube mounting

PSD-S ME OB/MB - Mounting material



2700155

<https://www.phoenixcontact.com/us/products/2700155>

Mounting position	any
-------------------	-----

PSD-S ME OB/MB - Mounting material


2700155

<https://www.phoenixcontact.com/us/products/2700155>



Drawings

Dimensional drawing



PSD-S ME OB/MB - Mounting material



2700155

<https://www.phoenixcontact.com/us/products/2700155>

Classifications

ECLASS

ECLASS-13.0	27371232
ECLASS-15.0	27371232

ETIM

ETIM 9.0	EC001152
----------	----------

UNSPSC

UNSPSC 21.0	46171600
-------------	----------

2700155

<https://www.phoenixcontact.com/us/products/2700155>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	fae72cf1-8973-4464-b489-08a1ace9a10b

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com