

VS-08-T-H-RJ45/IP67 - RJ45 sleeve housing



1652732

<https://www.phoenixcontact.com/us/products/1652732>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 sleeve housing, design: RJ45, degree of protection: IP67, number of positions: 8, material: PA, cable outlet: straight, color: traffic grey A RAL 7042, Ethernet

Your advantages

- Simple operation
- IP65/67
- High-quality and inexpensive solution in the IP protection zone

Commercial data

Item number	1652732
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	AB17
Product key	ABNNAZ
GTIN	4017918952877
Weight per piece (including packing)	13.92 g
Weight per piece (excluding packing)	13.265 g
Customs tariff number	85389099
Country of origin	DE

VS-08-T-H-RJ45/IP67 - RJ45 sleeve housing



1652732

<https://www.phoenixcontact.com/us/products/1652732>

Technical data

Product properties

Product type	Sleeve housings
Type	RJ45
Sensor type	Ethernet
Number of positions	8
No. of cable outlets	1
Cable outlet	straight

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage (III/3)	72 V (DC)
-----------------------	-----------

Dimensions

Width	38.4 mm
Height	19.9 mm
Length	45 mm

Material specifications

Color	traffic grey A RAL 7042
Flammability rating according to UL 94	V0
Housing material	PA
Cable seal material	NBR
O-ring material	FPM

Cable/line

External cable diameter	5 mm ... 8.5 mm
-------------------------	-----------------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 1000
-----------------------------	--------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 80 °C

VS-08-T-H-RJ45/IP67 - RJ45 sleeve housing



1652732

<https://www.phoenixcontact.com/us/products/1652732>

Classifications

ECLASS

ECLASS-15.0	27440192
ECLASS-13.0	27440192

ETIM

ETIM 9.0	EC002943
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

VS-08-T-H-RJ45/IP67 - RJ45 sleeve housing



1652732

<https://www.phoenixcontact.com/us/products/1652732>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	ec5ae543-8bba-46c8-9174-07965d2283c9

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com