

FTP SCREW M3X4,5 - Screw



3069467

<https://www.phoenixcontact.com/us/products/3069467>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Screw, for attaching cable lugs to FAME test plugs, with cover, without test pick-off, height: 4.5 mm, color: silver/black

Commercial data

Item number	3069467
Packing unit	30 pc
Minimum order quantity	30 pc
Sales key	BE01
Product key	BE611Z
GTIN	4055626166865
Weight per piece (including packing)	1 g
Weight per piece (excluding packing)	1 g
Customs tariff number	74152900
Country of origin	PL

FTP SCREW M3X4,5 - Screw

3069467

<https://www.phoenixcontact.com/us/products/3069467>



Technical data

Product properties

Product type	Test socket
--------------	-------------

Connection data

Screw thread	M3
Tightening torque	... 0.6 Nm

Dimensions

Height	4.5 mm
--------	--------

Material specifications

Color	multicolored (RAL -)
	silver-colored
	black (RAL 9005)
Material	Brass
Insulating material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 85 °C
Ambient temperature (storage/transport)	-25 °C ... 55 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

FTP SCREW M3X4,5 - Screw



3069467

<https://www.phoenixcontact.com/us/products/3069467>

Classifications

ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27141190

ETIM

ETIM 9.0	EC004591
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FTP SCREW M3X4,5 - Screw



3069467

<https://www.phoenixcontact.com/us/products/3069467>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com