

3202999

https://www.phoenixcontact.com/us/products/3202999

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assortment box, supplied with TWIN ferrules in accordance with DIN 46228-4, 20 pcs. AI-TWIN 2x4-12 GY, 10 pcs. each AI-TWIN 2x6-14 YE, AI-TWIN 2x10-14 RD

Your advantages

- · Color coding and the transparent cover facilitate fast access to the required ferrules
- · The practical assortment boxes are designed to keep your workshop tidy
- · Using the integrated euro-clip, they can be hung up on perforated board walls, for example, to save space

Commercial data

Item number	3202999
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH34
Product key	BH3416
GTIN	4017918947125
Weight per piece (including packing)	100.42 g
Weight per piece (excluding packing)	100.42 g
Customs tariff number	85369010
Country of origin	DE



3202999

https://www.phoenixcontact.com/us/products/3202999

Set consists of

AI-TWIN 2X 4 -12 GY - Ferrule

3201000

https://www.phoenixcontact.com/us/products/3201000



Ferrule, Length contact range: 12 mm, sleeve length: 23 mm, color: gray

AI-TWIN 2X 6 -14 YE - Ferrule

3201013

https://www.phoenixcontact.com/us/products/3201013



Ferrule, Length contact range: 14 mm, sleeve length: 25 mm, color: yellow



3202999

https://www.phoenixcontact.com/us/products/3202999

AI-TWIN 2X10 -14 RD - Ferrule

3201026

https://www.phoenixcontact.com/us/products/3201026



Ferrule, Length contact range: 14 mm, sleeve length: 26 mm, color: red



3202999

https://www.phoenixcontact.com/us/products/3202999

Technical data

Product properties

	Product type	Assortment box		
Material specifications				
	Color	gray (RAL 7042)		
	Material	CU-DHP		
	Flammability rating according to UL 94	НВ		
	Coating	galvanically tin-plated		
	Components	free from silicone and halogen		



3202999

https://www.phoenixcontact.com/us/products/3202999

Classifications

ECLASS

	ECLASS-13.0	27400218		
	ECLASS-15.0	27400218		
ETIM				
LIN				
	ETIM 9.0	EC000524		
UNSPSC				
5.15. 55				
	UNSPSC 21.0	39121400		



3202999

https://www.phoenixcontact.com/us/products/3202999

Environmental product compliance

EU RoHS

E O NOTIO				
Fulfills EU RoHS substance requirements	Yes, No exemptions			
China RoHS				
Environment friendly use period (EFUP)	EFUP-E			
	No hazardous substances above the limits			
EU REACH SVHC				
REACH candidate substance (CAS No.)	No substance above 0.1 wt%			

Phoenix Contact 2025 @ - all rights reserved https://www.phoenixcontact.com

Phoenix Contact USA 586 Fulling Mill Road Middletown, PA 17057, United States (+717) 944-1300 info@phoenixcon.com