

THERMOMARK-RIBBON 110 - Ink ribbon



5145384

<https://www.phoenixcontact.com/us/products/5145384>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ink ribbon, for roll printers for printing product groups TML..., TMT..., WML..., WML HF..., WML-FLAG..., WMT..., WMTB..., EML..., EMLC ..., EML-ESD..., EMLF ..., EML-HA ..., EML-LPR(D) ... , EML-LT ..., EMLP..., EML-RM..., EML-RS ..., EMLS..., EMT..., PML-GHS..., PML-T..., PML-P..., PML-W..., PMM..., length: 300 m, roll length: 300 m, width: 110 mm, color: black

Commercial data

Item number	5145384
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG02
Product key	BG1223
GTIN	4046356107471
Weight per piece (including packing)	346.4 g
Weight per piece (excluding packing)	346.4 g
Customs tariff number	96121010
Country of origin	CN

THERMOMARK-RIBBON 110 - Ink ribbon



5145384

<https://www.phoenixcontact.com/us/products/5145384>

Technical data

Product properties

Product type	Ink ribbon
--------------	------------

Marking

Identification technology	Thermal transfer
---------------------------	------------------

Dimensions

Width	110 mm
Length	300 m
Length of roll	300 m

Material specifications

Color	black (RAL 9005)
Material	Polyester

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	5 °C ... 35 °C
Permissible humidity (operation)	30 % ... 85 %
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	24 months after production date.

THERMOMARK-RIBBON 110 - Ink ribbon



5145384

<https://www.phoenixcontact.com/us/products/5145384>

Classifications

ECLASS

ECLASS-13.0	19140614
ECLASS-15.0	19140614

ETIM

ETIM 9.0	EC001694
----------	----------

UNSPSC

UNSPSC 21.0	44103100
-------------	----------

THERMOMARK-RIBBON 110 - Ink ribbon



5145384

<https://www.phoenixcontact.com/us/products/5145384>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com