

## Power Extension Cord, NEMA 5-15P to NEMA 5-15R - Heavy-Duty, 15A, 120V, 14 AWG, 10 ft. (3.05 m), Black

MODEL NUMBER: P024-010



10 ft. extension cord connects your computer or other device with a NEMA 5-15P plug to a PDU or UPS with a NEMA 5-15R outlet.

### Features

**Heavy-Duty Extension Cable for Network Devices That Require a Heavy-Gauge Connection** This 10-ft. (3.05 m) extension cord features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. It can be used to connect a computer, monitor, printer or other device with a NEMA 5-15P plug to a wall outlet, PDU, surge protector or UPS system with a NEMA 5-15R outlet. The 10-ft. (3.05 m) length allows you great flexibility in placing equipment with respect to the power outlet.

### Highlights

- Recommended for powering computers, printers and other home/office peripherals
- 10-ft. (3.05 m) length allows great flexibility in placing devices in relationship to AC outlet
- Ideal replacement for worn-out or missing 10-ft. (3.05 m) extension cord

### Applications

- Connect devices like computers, servers and monitors to a PDU in your data center
- Extend an existing power connection up to 10-ft. (3.05 m) to more easily place a device or reach a power source in a rack
- Provide a high-quality replacement for a worn-out or missing power cord

### Package Includes

- P024-010 10-ft. (3.05 m) Extension Cord, NEMA 5-15P to NEMA 5-15R, Black

## Specifications

| OVERVIEW                    |                                                   |
|-----------------------------|---------------------------------------------------|
| UPC Code                    | 037332180612                                      |
| Device Compatibility        | Computer; Monitor/HDTV; Printer; Server; UPS; PDU |
| Country/Region              | North America                                     |
| INPUT                       |                                                   |
| Maximum Input Amps          | 15                                                |
| Voltage Compatibility (VAC) | 125                                               |
| CONNECTIONS                 |                                                   |
| Side A - Connector 1        | NEMA 5-15P                                        |
| Side B - Connector 1        | NEMA 5-15R                                        |



Powering Business Worldwide

TRIPP LITE  
SERIES

| PHYSICAL                            |                             |
|-------------------------------------|-----------------------------|
| Plug Color                          | Black                       |
| Cable Jacket Color                  | Black                       |
| Cable Jacket Material               | PVC                         |
| Cable Jacket Rating                 | VW-1                        |
| Power Cord Jacket Type              | SJT                         |
| Cable Outer Diameter (OD)           | 9.3mm                       |
| Number of Conductors                | 3                           |
| Wire Gauge (AWG)                    | 14                          |
| Wire Gauge (OD - mm <sup>2</sup> )  | 2.08                        |
| Cable Length (ft.)                  | 10                          |
| Cable Length (m)                    | 3.05                        |
| Shipping Dimensions (hwd / in.)     | 1.00 x 7.00 x 11.00         |
| Shipping Dimensions (hwd / cm)      | 2.54 x 17.78 x 27.94        |
| Shipping Weight (lbs.)              | 1.10                        |
| Shipping Weight (kg)                | 0.50                        |
| ENVIRONMENTAL                       |                             |
| Operating Temperature Range         | -4° to 140°F (-20° to 60°C) |
| Storage Temperature Range           | -4° to 140°F (-20° to 60°C) |
| Operating Humidity Range            | 10% to 65% RH               |
| Storage Humidity Range              | 10% to 65% RH               |
| FEATURES & SPECIFICATIONS           |                             |
| Antibacterial                       | No                          |
| Angled Plug                         | No                          |
| High Voltage                        | No                          |
| Locking Plug                        | No                          |
| Coiled Power Cord                   | No                          |
| STANDARDS & COMPLIANCE              |                             |
| Product Certifications              | cUL Listed; UL Listed       |
| Product Compliance                  | RoHS                        |
| WARRANTY & SUPPORT                  |                             |
| Product Warranty Period (Worldwide) | Lifetime limited warranty   |



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.