


mSATA SSD to 2.5 in. SATA Enclosure Adapter Converter

MODEL NUMBER: **P960-001-MSATA**



Access an mSATA solid state drive (SSD) with a standard SATA computer, SATA drive enclosure or docking station by converting it into a 2.5 in. SATA SSD.

Description

The P960-001-MSATA mSATA SSD to 2.5 in. SATA Enclosure Adapter Converter lets you use an mSATA SSD with a standard SATA-enabled computer, drive enclosure or docking station. To share data, just remove the adapter's cover, connect the drive to the mSATA connector, secure it with the included screws, put the cover back, and connect the adapter to your computer's SATA port. Or connect it to your computer's USB port using a USB docking station, such as U339-000 (sold separately).

The enclosed housing protects the drive when used in applications requiring more durability, such as hot-swap drive bays and external docking stations. The P960-001-MSATA supports SATA I, II and III drives and data transfer rates up to 6 Gbps. It's plug-and-play, so no software, drivers or external power supply are required.

Features

Use an mSATA SSD as a Standard 2.5 in. SATA SSD

- Access an mSATA drive with a standard SATA computer, drive enclosure or docking station
- Supports SATA I, II and III SSDs (1.5/3.0/6.0 Gbps)
- Maximizes SATA III controller capabilities to boost data transfer speeds up to 6 Gbps
- Enclosed housing protects drive in applications requiring more durability
- High-efficiency mSATA SSD reduces system's power consumption
- Plug-and-play with no software, drivers or external power supply needed
- Works with USB-enabled SATA docking stations, such as U339-000 (sold separately)

Specifications

OVERVIEW	
UPC Code	037332199249
Technology	SATA/eSATA

Highlights

- Boosts computer performance by adding mSATA SSD speed
- Supports SATA I, II and III SSDs (1.5/3.0/6.0 Gbps)
- Enclosed housing protects drive
- Reduces system's power consumption
- Plug-and-play—no software, drivers or external power supply

System Requirements

- mSATA drive
- SATA host device

Package Includes

- P960-001-MSATA mSATA SSD to 2.5 in. SATA Enclosure Adapter Converter
- Mounting hardware
- Screwdriver
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Shipping Dimensions (hwd / in.)	1.00 x 4.80 x 6.50
Shipping Dimensions (hwd / cm)	2.54 x 12.19 x 16.51
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty
Product Warranty Period (U.S. & Canada)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.