

P-CO 2-5 R47K - Component connector



3032447

<https://www.phoenixcontact.com/us/products/3032447>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Your advantages

- The component connector can easily plug into the bridge shaft of two adjacent CLIPLINE complete terminal blocks with a 5.1 mm pitch.

Commercial data

Item number	3032447
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2Z3X
GTIN	4046356981606
Weight per piece (including packing)	1.45 g
Weight per piece (excluding packing)	1.45 g
Customs tariff number	85366990
Country of origin	PL

P-CO 2-5 R47K - Component connector



3032447

<https://www.phoenixcontact.com/us/products/3032447>

Technical data

Notes

General	Can be used between two neighboring CLIPLINE complete terminal blocks with 2.5 mm ² conductor cross-section
---------	--

Product properties

Product type	Component plug terminal block
Number of positions	2
Pitch	5.2 mm

Dimensions

Width	4.1 mm
Height	8.9 mm
Depth	34.8 mm
Pitch	5.2 mm

Material specifications

Color	black (RAL 9005)
Material	PA

Electrical tests

Surge voltage test

Test voltage setpoint	9.8 kV
Result	Test passed

Power-frequency withstand voltage

Test voltage setpoint	2 kV
Result	Test passed

P-CO 2-5 R47K - Component connector



3032447

<https://www.phoenixcontact.com/us/products/3032447>

Classifications

ECLASS

ECLASS-13.0	27250305
ECLASS-15.0	27250305

ETIM

ETIM 9.0	EC002018
----------	----------

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

P-CO 2-5 R47K - Component connector



3032447

<https://www.phoenixcontact.com/us/products/3032447>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com