

External 36V 3U Rack/Tower Battery Pack for Select UPS Systems (BP36V42-3U)

MODEL NUMBER: **BP36V42-3U**



Highlights

- Extends the runtime of expandable 36V DC UPS Systems
- Included daisychain connector supports the addition of multiple compatible external battery packs
- Supports 3U rack-mount installation; 4-post installation accessories included
- Options for 2-post rack-mount and tower installation available

Package Includes

- BP36V42-3U external battery pack with attached DC cabling
- 4 post compatible mounting hardware
- Owner's manual

Description

BP36V42-3U rack/tower external battery pack offers extended battery runtime when used in conjunction with expandable 36V rack-mount and tower UPS systems. Includes heavy-gauge cabling with high-current DC connector for safe, simple installation. Included daisy-chain connector enables the connection of additional compatible 36V external battery packs to the host UPS. Included mounting accessories support 3U rack-mount installation in 4-post racks. Options for 2-post center-mounting and upright tower installation available.

Compatible with SMART1000RML2U, SMART1200XLHG, SMART1500RML2UA, SMART1500RMLN, SMART1500XL, SMX1200XLHG, SMX1500XLRT2U and other UPS systems that specify the use of this battery pack.

Features

- Offers extended-run UPS operation when used in conjunction with compatible 36V DC UPS systems
- Includes heavy-gauge cabling with high-current DC connectors for simple installation
- Daisychain connector enables the connection of additional compatible 36V external battery packs to the host UPS
- Included mounting brackets support rack-mount installation in 4-post racks using only 3 rack spaces (3U)
- 2POSTRMKITHD option supports balanced two-point center-mounting in 2-post equipment racks
- 2-USTAND option enables upright tower placement

Specifications

OVERVIEW	
UPC Code	037332123312
INPUT	
Input Phase	Single-Phase



Powering Business Worldwide

TRIPP LITE
SERIES

BATTERY	
Expandable Runtime	Yes
DC System Voltage (VDC)	36
UPS Connection	Detachable cable with UPS specific DC connector (36 in length, 6 gauge)
Typical Battery Lifespan	4-6 years typical (North America)
PHYSICAL	
Material of Construction	Steel
Rack Height	3U
External Battery Pack Form Factor	Rack/Tower
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (2POSTRMKITWM); Wallmount (2POSTRMKITWM)
Minimum Required Rack Depth (cm)	71.12
Minimum Required Rack Depth (inches)	28
Optional Mounting Accessory Notes	2POSTRMKITWM ; enables wall-mount and 2-post rackmount installation
Shipping Dimensions (hwd / in.)	12.00 x 23.00 x 33.00
Shipping Dimensions (hwd / cm)	30.48 x 58.42 x 83.82
Shipping Weight (lbs.)	185.00
Shipping Weight (kg)	83.91
Unit Dimensions (hwd / in.)	5.250 x 17.500 x 25.000
Unit Dimensions (hwd / cm)	13.3 x 44.45 x 63.5
Unit Weight (lbs.)	174.1
Unit Weight (kg)	78.97
Mounting Details	Included 4POSTRAILKIT mounting bracket enables installation in 4 post racks from 20.5 to 36 inches (521 to 914mm)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe)
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

Product Warranty Period (Puerto Rico)	1-year limited warranty
---------------------------------------	-------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.