


Portable Digital Signage Stand for 23" to 42" Flat-Screen Displays

MODEL NUMBER: DMPDS2342TRIC



Tripod-style portable TV stand sets up quickly for delivering your message in a classroom, lobby or anywhere else with heavy foot traffic.

Features

Set Up Your Digital Signage Wherever Your Audience Is

This portable TV stand fits most flat-panel displays, whiteboards and monitors from 23 to 42 inches (58 to 107 centimeters). It assembles easily to allow convenient setup wherever foot traffic flows, such as classrooms, trade shows, lecture halls, offices, auditoriums, restaurants, bars and hotels. The tripod-style stand adjusts to five different heights, and the display tilts for comfortable custom viewing.

Durable Steel Frame Designed to Last

The frame withstands the stress of repeated adjustments and supports up to 77 pounds (35 kilograms). Use the easy-grip knobs and security pin to lock the frame into place and protect the display against tipping. Because the tripod folds when not in use, the DMPDS2342TRIC is easy to transport and store.

VESA-Compliant Mounting Ensures Display Compatibility

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this mount supports the following VESA mounting hole patterns: 75 x 75, 100 x 100, 200 x 100 and 200 x 200. All hardware is included.

Highlights

- Supports most monitors, whiteboards and interactive displays from 23 to 42 in.
- Durable steel frame blends into any room decor and supports up to 77 lb.
- Tripod-style stand adjusts to different heights for comfortable custom viewing
- Easy-grip knobs and security pin lock stand into place and ensure display's safety

Applications

- Bring a digital whiteboard or interactive display into a conference room or classroom for a virtual meeting or brainstorming session
- Move a flat-panel display into a lobby, hallway or trade show booth to create temporary digital signage
- Show videos in a multipurpose area, such as a hotel lobby or lecture hall, where a permanent display is impractical
- Fold the stand and store it in a secure area when not in use

System Requirements

Flat-screen television, monitor, digital whiteboard or interactive display from 23 to 42 in.

Package Includes

- DMPDS2342TRIC Portable Digital Signage Stand
- Assembly hardware
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332263841
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Steel



Powering Business Worldwide

TRIPP LITE
SERIES

VESA Pattern (mm)	75x75; 100x100; 200x100; 200x200
Motion	Fixed
Mounting Location	Floor
Minimum Screen Size (in.)	23
Minimum Screen Size (cm)	58.42
Maximum Screen Size (in.)	42
Maximum Screen Size (cm)	106.7
Maximum Weight Capacity (lbs.)	77
Maximum Weight Capacity (kg)	35
Number of Displays	1
Unit Dimensions (hwd / in.)	70.900 x 8.700 x 9.100
Unit Dimensions (hwd / cm)	180 x 22 x 23
Unit Weight (lbs.)	77
Unit Weight (kg)	34.93
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.