

## 4x 12V 9AH UPS Replacement Battery Cartridge Kit for Select Best, Powerware, Liebert and Other UPS

MODEL NUMBER: **RBC54**



### Highlights

- Up to 30% longer runtime than basic replacements
- OEM certified premium batteries
- Rugged, leakproof construction
- Maintenance-free
- Wide operating temperature range

### Package Includes

- 4 12V UPS replacement batteries
- Instruction manual with installation, recycling and warranty information

### Description

These premium UPS replacement battery cartridges breathe new life into UPS systems suffering from expired or weak internal batteries. Each replacement battery cartridge is carefully screened and certified to meet or exceed original manufacturer specifications and ships ready for installation into your UPS system. Reusable packaging holds expired batteries for recycling center delivery. Compatible with a wide variety UPS brands and models. See the UPS replacement battery web page to confirm compatibility and quantity required.

### Features

- Restores UPS runtime performance to its original runtime specifications
- Reusable packaging contains expired batteries for recycling center delivery
- Compatible with a variety of UPS brands

## Specifications

| OVERVIEW                        |                                                 |
|---------------------------------|-------------------------------------------------|
| UPC Code                        | 037332118691                                    |
| BATTERY                         |                                                 |
| Included Battery Set            | Contains (4) 12V 9AH sealed lead acid batteries |
| Typical Battery Lifespan        | 3 - 5 years, depending on host UPS conditions   |
| PHYSICAL                        |                                                 |
| Shipping Dimensions (hwd / in.) | 6.80 x 7.00 x 13.70                             |
| Shipping Dimensions (hwd / cm)  | 17.27 x 17.78 x 34.80                           |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                         |                                                            |
|-----------------------------------------|------------------------------------------------------------|
| Shipping Weight (lbs.)                  | 26.80                                                      |
| Shipping Weight (kg)                    | 12.16                                                      |
| Unit Dimensions (hwd / in.)             | 4.000 x 2.500 x 6.000                                      |
| Unit Dimensions (hwd / cm)              | Set of 4 batteries; Each battery measures 9.4 x 6.4 x 14.9 |
| Unit Weight (lbs.)                      | 6                                                          |
| Unit Weight (kg)                        | 2.72                                                       |
| <b>ENVIRONMENTAL</b>                    |                                                            |
| Relative Humidity                       | 0-95% non-condensing                                       |
| Operating Elevation                     | 0-10000 ft. (0-3000 m)                                     |
| Storage Elevation (ft.)                 | 0 - 50,000                                                 |
| Storage Elevation (m)                   | 0 - 15,200 m                                               |
| <b>STANDARDS &amp; COMPLIANCE</b>       |                                                            |
| Product Compliance                      | RoHS                                                       |
| <b>WARRANTY &amp; SUPPORT</b>           |                                                            |
| Product Warranty Period (U.S. & Canada) | 18-month limited warranty                                  |
| Product Warranty Period (International) | 1-year limited warranty                                    |
| Product Warranty Period (Mexico)        | 1-year limited warranty                                    |
| Product Warranty Period (Puerto Rico)   | 1-year limited warranty                                    |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.