

aux. switch module, rotary op. 2 x leading to "ON" and 1 x leading to "OFF"  
accessory for: 3VA52/53/53; 3VA61-64



Model	
product brand name	SETRON
product designation	Auxiliary switch module, rotary operator
accessories	Auxiliary switch module
General technical data	
degree of pollution	3
overvoltage category	III
Voltage	
surge voltage resistance	4 kV
operating voltage / at AC / according to CSA and UL	230 V
operating voltage / at DC / according to CSA and UL	24 V
operating voltage / at AC / at 50 Hz / rated value / minimum	230 V
operating voltage / at DC / rated value / minimum	250 V
Current	
thermal current	5 A
operational current	
• at AC-12 / at 12 V	5 A
• at AC-12 / at 24 V	5 A
• at AC-12 / at 48 V	5 A
• at AC-12 / at 125 V	5 A
• at AC-12 / at 220/240 V	5 A
• at DC-13 / at 12 V	0.2 A
• at DC-13 / at 24 V	0.2 A
• at DC-13 / at 48 V	0.2 A
• at DC-13 / at 110 V	0.2 A
• at DC-13 / at 250 V	0.2 A
• at AC-15 / at 12 V	2 A
• at AC-15 / at 24 V	2 A
• at AC-15 / at 48 V	2 A
• at AC-15 / at 125 V	2 A
• at AC-15 / at 220/240 V	2 A
Mechanical Design	
height	41.85 mm
width	88.5 mm
depth	70 mm
ambient temperature / during operation	
• minimum	-25 °C
• maximum	70 °C
ambient temperature / during storage	
• minimum	-40 °C

- maximum

80 °C

#### ambient temperature / during storage

- minimum
- maximum

-40 °C

80 °C

#### Certificates

##### General Product Approval



[Miscellaneous](#)



##### EMV

##### Marine / Shipping

##### other

##### Environment



[Miscellaneous](#)

[Confirmation](#)

[Miscellaneous](#)



#### Environment

[Environmental Con-  
firmations](#)

[Environmental Con-  
firmations](#)

#### Further information

##### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

##### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9477-0GX20>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9477-0GX20>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3VA9477-0GX20](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9477-0GX20)

##### CAX-Online-Generator

<http://www.siemens.com/cax>

##### Tender specifications

<http://www.siemens.com/specifications>



