



plug-in socket for PT relay, 2 changeover contacts, screw terminal

product type designation	LZS
General technical data	
display version LED	No
switching behavior	monostable
reference code according to IEC 81346-2	U
Substance Prohibitance (Date)	05/01/2012
Weight	0.051 kg
Switching Function	
design of the switching function	changeover switch
Mechanical data	
product component plug-in socket	Yes
design of the snap-on socket base	Standard socket
design of the relay operating mechanism	poled
Auxiliary circuit	
number of NC contacts for auxiliary contacts	0
number of NO contacts for auxiliary contacts	0
number of CO contacts for auxiliary contacts	0
Connections/ Terminals	
product function removable terminal	No
type of electrical connection	screw terminal
type of connectable conductor cross-sections - solid - finely stranded with core end processing - for AWG cables solid	1x (1,0 ... 2,5), 2x 1,0, 2x 1,5, 2x 2,5 1x (1,0 ... 1,5), 2x 1,0, 2x 1,5 1x (18 ... 14), 2x 18, 2x 16, 2x 14
connectable conductor cross-section - solid - finely stranded with core end processing	1 ... 2.5 mm ² 1 ... 1.5 mm ²
AWG number as coded connectable conductor cross section solid	18 ... 14
tightening torque with screw-type terminals	0.5 ... 0.7 N·m
Installation/ mounting/ dimensions	
mounting position	any
fastening method	snap-on mounting
height	74 mm
width	27 mm
depth	41.5 mm
Ambient conditions	
ambient temperature during operation	-40 ... +70 °C

- during storage
- during transport

-25 ... +70 °C

-25 ... +70 °C

Approvals Certificates

General Product Approval

Maritime application

other



[Confirmation](#)

Environment

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=LZS:PT78720>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=LZS:PT78720>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


<https://support.industry.siemens.com/cs/ww/en/ps/LZS:PT78720>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=LZS:PT78720&lang=en







last modified:

4/2/2025 