



## Slot stone -N-

- This slot stone slides into the end of the profile slot

**Material:** Galvanised steel



[mm]



| Code No. | Type | lot sizes         | Slot geometry        | A | B  | C  | D  | E | M  |
|----------|------|-------------------|----------------------|---|----|----|----|---|----|
| 4006201  | M5   | 10, 20, 30... pcs | 30                   | 5 | 10 | 13 | 13 | 3 | M5 |
| 4006203  | M6   | 10, 20, 30... pcs | 30                   | 5 | 10 | 13 | 13 | 3 | M6 |
| 4006202  | M8   | 10, 20, 30... pcs | 30                   | 5 | 10 | 13 | 13 | 3 | M8 |
| 4026207  | M5   | 10, 20, 30... pcs | 40                   | 8 | 10 | 13 | 15 | 4 | M5 |
| 4026203  | M6   | 10, 20, 30... pcs | 40                   | 8 | 10 | 13 | 15 | 4 | M6 |
| 4009202  | M8*  | 10, 20, 30... pcs | 30                   | 5 | 10 | 13 | 13 | 3 | M8 |
| 4026206  | M8   | 10, 20, 30... pcs | 40                   | 8 | 10 | 13 | 15 | 4 | M8 |
| 4029206  | M8*  | 10, 20, 30... pcs | 40                   | 8 | 10 | 13 | 15 | 4 | M8 |
| 4026214  | M8   | 10, 20, 30... pcs | 40                   | 8 | 10 | 28 | 15 | 4 | M8 |
| 4026208  | M8   | 10, 20, 30... pcs | 40, with screw M8x16 | 8 | 10 | 13 | 15 | 4 | M8 |
| 4026202  | M8   | 10, 20, 30... pcs | 40, with screw M8x18 | 8 | 10 | 13 | 15 | 4 | M8 |

\* Stainless steel

## Slot stone -NF-

- This slot stone slides into the end of the profile slot
- The spring clip guarantees fixation in any position/installation position

**Material:** Galvanised steel



[mm]

| Code No. | Type | lot sizes         | Slot geometry | A | B  | C  | D  | E | M  |
|----------|------|-------------------|---------------|---|----|----|----|---|----|
| 4016241  | M5   | 10, 20, 30... pcs | 40            | 8 | 10 | 13 | 15 | 4 | M5 |
| 4016242  | M6   | 10, 20, 30... pcs | 40            | 8 | 10 | 13 | 15 | 4 | M6 |
| 4016243  | M8   | 10, 20, 30... pcs | 40            | 8 | 10 | 13 | 15 | 4 | M8 |