



Product: [9921](#)

Lead Wire, #22 Str TC, PVC Ins, AWM 1007 AWM 1569

[Request Sample](#)

Product Description

Low Temp Plastic Lead Wire, 22AWG (7x30) Tinned Copper, PVC Insulation, AWM 1007 AWM 1569 CSA TYPE TR-64 TRSR-64

Technical Specifications

Product Overview

Suitable Applications:	inter-connection circuits, internal wiring of computer and electronic equipments, internal wiring of appliances
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	1	22 AWG	7x30	TC - Tinned Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter
PVC - Polyvinyl Chloride	0.017 in (0.43 mm)	0.062 in (1.6 mm)

Overall Cable Diameter (Nominal):	0.062 in (1.6 mm)
-----------------------------------	-------------------

Electrical Characteristics

Electricals

Nom. Conductor DCR	Max. Current
18.1 Ohm/1000ft	Single conductor in free air @ 30°C: 11 A

Voltage

UL Voltage Rating
300 V RMS

Mechanical Characteristics

Temperature

UL Temperature	Operating
105°C	-20°C To +105°C

Bend Radius

Stationary Min.	Installation Min.
0.62 in (16 mm)	0.62 in (16 mm)

Max. Pull Tension:	9 lbs (4.1 kg)
Bulk Cable Weight:	4 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	VW-1
AWM Compliance:	AWM 1007, AWM 1569

CEC / C(UL) Compliance:	TRSR-64
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.511 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
9921 010100	Black	Reel	100 ft	612825263210	
9921 0101000	Black	Reel	1,000 ft	612825263227	P
9921 0105000	Black	Reel	5,000 ft	612825263234	C
9921 013100	Blue, Dark	Reel	100 ft	612825263258	
9921 0131000	Blue, Dark	Reel	1,000 ft	612825263265	P
9921 0135000	Blue, Dark	Reel	5,000 ft	612825263272	C
9921 006100	Blue, Light	Reel	100 ft	612825263098	
9921 0061000	Blue, Light	Reel	1,000 ft	612825263104	P
9921 001100	Brown	Reel	100 ft	612825262985	
9921 0011000	Brown	Reel	1,000 ft	612825262992	P
9921 008100	Gray	Reel	100 ft	612825263135	
9921 0081000	Gray	Reel	1,000 ft	612825263142	P
9921 0085000	Gray	Reel	5,000 ft	612825263159	C P
9921 005100	Green, Dark	Reel	100 ft	612825263074	
9921 0051000	Green, Dark	Reel	1,000 ft	612825263081	P
9921 003100	Orange	Reel	100 ft	612825263029	
9921 0031000	Orange	Reel	1,000 ft	612825263036	P
9921 002100	Red	Reel	100 ft	612825263005	
9921 0021000	Red	Reel	1,000 ft	612825349860	P
9921 0025000	Red	Reel	5,000 ft	612825349877	C P
9921 007100	Violet	Reel	100 ft	612825263111	
9921 0071000	Violet	Reel	1,000 ft	612825263128	P
9921 009100	White	Reel	100 ft	612825263173	
9921 0091000	White	Reel	1,000 ft	612825263180	P
9921 004100	Yellow	Reel	100 ft	612825263043	
9921 0041000	Yellow	Reel	1,000 ft	612825263050	P
9921 0045000	Yellow	Reel	5,000 ft	612825263067	C

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.