


APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/16/21	
A		ADDED SILICON TYPE	11/14/22	



PLUG SIZE	MATERIAL
1 = SIZE 1	T = TPU
	S = SILICONE

CABLE I.D. "A"
30 = 3.0mm (TPU)
35 = 3.5mm (TPU)
40 = 4.0mm (TPU)
45 = 4.5mm (TPU)
50 = 5.0mm (TPU)
55 = 5.5mm (TPU)
60 = 6.0mm (TPU or SILICONE)
65 = 6.5mm (TPU or SILICONE)

COLOR
B = BLACK (TPU or SILICONE)
G = GRAY (TPU)
GR = GREEN (TPU)
Y = YELLOW (TPU)
R = RED (TPU)
BU = BLUE (TPU or SILICONE)
WT = WHITE (SILICONE)

Cable Dia. "A"	Min. ϕ	Max. ϕ
30	.118 [3.0]	.134 [3.4]
35	.138 [3.5]	.153 [3.9]
40	.157 [4.0]	.173 [4.4]
45	.177 [4.5]	.197 [5.0]
50	.197 [5.0]	.216 [5.5]
55	.216 [5.5]	.205 [6.0]
60	.205 [6.0]	.256 [6.5]
65	.256 [6.5]	.275 [7.0]

SPECIFICATIONS:

Material:

TPU (Available sizes 30, 35, 40, 45, 50, 55, 60 & 65),
Color Black, Gray, Green, Yellow, Red, Blue

Silicone (Available sizes 60 & 65), Color Black, Blue & white

Temperature Rating:

Operating temperature: TPU: -40°C to +80°C
Silicone: -60°C to +200°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X $\pm$.10 ϕ X $\pm$.10
.XX $\pm$.020 ϕ XX $\pm$.015
.XXX $\pm$.015 ϕ XXX $\pm$.010

APPROVALS		DATE
DRAWN	SS	8/16/21
CHECKED	SS	8/16/21
APPROVED		

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE			
BEND RELIEF FOR PLUG, SIZE 1			
SIZE X	PART NO. MMI-BR1-XX-XX-X		REV. A
REF:	SXXXXX	SCALE: NTS	SHEET 1 OF 1