



Representative Image

## Catalog No. RMS18312HRLR

Description: MTR STACK 3-125A 1PH-1PH RNgLS 42-100K

UPC No 783164683707

Home > Modular Metering > ReliaMod&Trade; > ReliaMod Meter Module

### Descriptors

|          |                       |
|----------|-----------------------|
| Category | ReliaMod Meter Module |
|----------|-----------------------|

### Specifications

|                                                       |                                                                                                                                                                                                                                                                                                                 |
|-------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Additional Notes                                      | For tenant breaker load lugs, please refer to breaker specifications                                                                                                                                                                                                                                            |
| Depth (Inches)                                        | 9.5                                                                                                                                                                                                                                                                                                             |
| Enclosure                                             | N3R Outdoor                                                                                                                                                                                                                                                                                                     |
| Estimated Weight (lbs)                                | 102                                                                                                                                                                                                                                                                                                             |
| Height (Inches)                                       | 45.2                                                                                                                                                                                                                                                                                                            |
| Horizontal Bus Amperage                               | 800 A                                                                                                                                                                                                                                                                                                           |
| Main Phase Input                                      | 1-Phase                                                                                                                                                                                                                                                                                                         |
| Meter Mod III to ReliaMod Horizontal Bus Connections  | ABB ReliaMod horizontal bus does not match up to GE Meter Mod III horizontal bus, so any ReliaMod section cannot be connected to any GE Meter Mod III section and vice versa without a bus transition adapter section. Please refer to the ReliaMod bus transition adapters in the Buylog for more information. |
| Meter Module Tenant Breaker Provisions                | Only Accepts 42-100 KAIC TEY/TEYF/TEYL Tenant Breakers                                                                                                                                                                                                                                                          |
| No of Sockets                                         | 3                                                                                                                                                                                                                                                                                                               |
| Socket Amperage                                       | 125 A                                                                                                                                                                                                                                                                                                           |
| Socket Bypass                                         | None                                                                                                                                                                                                                                                                                                            |
| Socket Factory Installed Jaw Configuration            | 5-Jaw                                                                                                                                                                                                                                                                                                           |
| Socket Phase Output                                   | 1-Phase                                                                                                                                                                                                                                                                                                         |
| Socket Type                                           | Ringless                                                                                                                                                                                                                                                                                                        |
| Tenant Ground Lugs (Per each socket) AWG/kcmil Al/Cu  | #14-2/0                                                                                                                                                                                                                                                                                                         |
| Tenant Neutral Lugs (Per each socket) AWG/kcmil Al/Cu | #14-2/0                                                                                                                                                                                                                                                                                                         |
| Voltage                                               | 120/240V                                                                                                                                                                                                                                                                                                        |
| Width (Inches)                                        | 13.9                                                                                                                                                                                                                                                                                                            |