



Product: [5120UL](#)

Fire Alarm, #14-2c BC, FPLR

Product Description

Fire Alarm Cable, Riser-FPLR, 2-14 AWG solid bare copper conductors with polypropylene insulation, PVC jacket with ripcord

Technical Specifications

Product Overview

Suitable Applications:	Fire Alarm, Monitor/Detection, Circuits: Audio, Control, Initiating, Notification
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	2	14 AWG	Solid	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PP - Polypropylene	0.010 in (0.25 mm)	0.0845 in (2.15 mm)	Black, Red

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PP - Polypropylene	0.017 in (0.43 mm)	0.205 in (5.21 mm)	Yes

Overall Cable Diameter (Nominal):	0.205 in (5.21 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
Conductor(s)	2.43 Ohm/1000ft	23 pF/ft (75 pF/m)	25 Amps per conductor @ 30°C

Voltage

UL Voltage Rating
300 V (FPLR)

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	-20°C to +75°C

Bend Radius

Stationary Min.	Installation Min.
1.64 in (41.7 mm)	1.64 in (41.7 mm)

Max. Pull Tension:	99 lbs (45 kg)
Bulk Cable Weight:	33 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Riser, Indoor
Flammability / Reaction to Fire:	UL 1666 Riser, IEEE 1202 FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 760, FPLR
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	6120UL

History

Update and Revision:	Revision Number: 0.459 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	UPC	Footnote
5120UL 0101000	Black	612825156994	
5120UL D151000	Blue	612825156963	C
5120UL 0061000	Blue	612825350767	
5120UL 0061000	Blue	612825350767	
5120UL 0051000	Green	612825350750	
5120UL 0051000	Green	612825350750	
5120UL 0031000	Orange	612825350743	
5120UL 0031000	Orange	612825350743	
5120UL 0021000	Red	612825336488	C
5120UL 002500	Red	612825156970	C
5120UL 0071000	Violet	612825350774	
5120UL 0071000	Violet	612825350774	
5120UL 0091000	White	612825350781	
5120UL 0091000	White	612825350781	
5120UL 0041000	Yellow	612825156987	

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.