



Product: [6000UE](#) 

Security & Sound, 2 Conductor 12 AWG BC, CL2P

Product Description

Security & Commercial Audio Cable, Plenum-CL2P 2-12 AWG stranded bare copper conductors with Flamarrest® insulation, Flamarrest® jacket with ripcord

Technical Specifications

Product Overview

Suitable Applications:	Intercom/PA Systems, Sound/Audio Systems
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	2	12 AWG	19x25	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.011 in (0.28 mm)	0.113 in (2.87 mm)	Black, White

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.252 in (6.40 mm)	Yes

Overall Cable Diameter (Nominal): 0.252 in (6.40 mm)

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Inductance	Max. Current
Conductor(s)	1.6 Ohm/1000ft	36 pF/ft (120 pF/m)	0.14 µH/ft (0.46 µH/m)	30 Amps per conductor @ 25°C

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	0°C to +75°C

Bend Radius

Stationary Min.	Installation Min.
2.5 in (64 mm)	2.5 in (64 mm)

Max. Pull Tension:	152 lbs (68.9 kg)
Bulk Cable Weight:	52 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor
----------------------------	-------------------------

Flammability / Reaction to Fire:	NFPA 262, UL 910 (Plenum), IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 725, CL2P
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	5000UH

History

Update and Revision:	Revision Number: 0.503 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
6000UE 010Z500	Black	ReelTuff Box	500 ft	612825166108	
6000UE 0101000	Black	Reel	1,000 ft	612825432913	
6000UE 010Z1000	Black	ReelTuff Box	1,000 ft	612825434108	
6000UE 010Z1000	Black	ReelTuff Box	1,000 ft	612825434108	
6000UE 877500	Natural	Reel	500 ft	612825383116	
6000UE 877Z500	Natural	ReelTuff Box	500 ft	612825166122	
6000UE 8771000	Natural	Reel	1,000 ft	612825166115	C
6000UE 877Z1000	Natural	ReelTuff Box	1,000 ft	612825434122	
6000UE 877Z1000	Natural	ReelTuff Box	1,000 ft	612825434122	
6000UE 0121000	Pink	Reel	1,000 ft	612825337904	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.