



## Main

Range of Product	OsiSense XC
Series name	Special format
Product or Component Type	Limit switch head
Device short name	ZC2J
Head type	Rotary head
Product Compatibility	XC2J
Associated lever	ZC2JY61 ZC2JY71
Associated body	ZC2JD2 ZC2JC2 ZC2JD1 ZC2JC1 ZC2JC28 ZC2JC18
Movement of operating head	Rotary
Type of operator	Stay put without operating lever stay put
Type of approach	Lateral approach, 2 directions

## Complementary

Switch actuation	From left and right CW and CCW
Positive opening	Without
Net Weight	0.46 lb(US) (0.21 kg)
Head material	Metal

## Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

## Ordering and shipping details

Category	22449-LIMIT SWITCHES,ACCESSORIES
Discount Schedule	T
GTIN	3389110323962
Returnability	No
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.89 in (4.8 cm)
Package 1 Width	1.97 in (5.0 cm)
Package 1 Length	3.74 in (9.5 cm)
Package 1 Weight	7.69 oz (218.0 g)
Unit Type of Package 2	S01

Number of Units in Package 2	14
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	7.13 lb(US) (3.233 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------