


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE		PHOSPODAR




PART NUMBER	LENGTH METER [FEET]
FCA-M2FC-SCS-02	2.0 [6.56]
FCA-M2FC-SCS-05	5.0 [16.40]
FCA-M2FC-SCS-10	10.0 [32.81]
FCA-M2FC-SCS-15	15.0 [49.21]

NOTES:

1. FC CONNECTOR 1 ASSEMBLY POLISH TYPE: UPC.
2. SC CONNECTOR 1 ASSEMBLY POLISH TYPE: UPC.
3. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION).

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS	DATE	 an INFINIT® brand		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	DRAWN BY K.GLEBOVA	04/18/22				
	CHECKED BY P.HOSPODAR	04/25/22	CATEGORY FIBER OPTICS			
	APPROVED BY P.HOSPODAR	04/25/22				
THIRD-ANGLE PROJECTION 			PRODUCT DESCRIPTION FIBER OPTIC PATCH CORD MM OM2 SIMPLEX 3.0mm FC/UPC-SC/UPC ARMORED LSZH BLACK			
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			SIZE A	CAGE CODE 43321	ITEM NO. FCA-M2FC-SCS	REV. A
COLOR VARIATIONS MAY OCCUR			SCALE: NONE		CAD FILE: FCA-M2FC-SCS.SLDDRW	SHEET 1 OF 1