

Monitor Wall Mount - Aluminum - For up to 34" (33.1lb/15kg) Displays

Product ID: ARMWALL



Wall-mount your computer monitor or flat-screen TV to free up space on your desk or table. This monitor wall mount supports displays up to 34". It swivels and tilts to enable you to adjust the angle of your screen and provide viewing flexibility.

The monitor wall mount helps you save space on your desk or table surface, by letting you securely wall-mount a computer monitor or LED / LCD TV from 13" to 34" in size and up to 33 lb. (15 kg) in weight. It's ideal for many different applications, including business meeting rooms, healthcare or financial settings. The monitor wall mount works well in office settings or workspaces that back against a wall.

The monitor wall mount makes it easy to change your screen position, so you can work more comfortably. It swivels +45 / - 45, enabling you to move your screen easily to the left or right. It also tilts freely +45 / - 45, which makes it easy to adjust the angle of your display up or down.

The aluminum monitor wall mount features slide-in wall plate construction for easy installation. To help keep your work area free of clutter, the monitor arm also features a cable clip that keep your cables neatly out of sight.

The ARMWALL is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Free up desk or table space in business, commercial, industrial or office settings

- Wall mount a computer monitor or flat-screen TV in meeting rooms, healthcare or financial settings
- Ideal in office settings or work spaces that back against a wall
- Create space and work more comfortably in home office settings

Features

- Wall mount a VESA (50x50, 75x75, 100x100) compatible display 13" to 34", flat screen, curved or ultrawide, with a max weight of 33.2 lb. (15 kg)
- Swivels +45 / - 45 to provide viewing flexibility
- Tilts freely +45 / - 45 allowing easy angle adjustment up or down
- Easy installation with slide-in wall plate construction
- Cable management

Hardware

Warranty	5 Years
Cable Management	Yes
Articulating	No
# of Displays Supported	1
Mounting Options	Wall-Mount
VESA Hole Pattern(s)	50x50
	75x75 mm
	100x100 mm

Performance

Weight Capacity (Per Display)	33.1 lb [15 kg]
Minimum Display Size	13"
Maximum Display Size	34"
Fits Curved Display	Yes
Fits UltraWide Displays	Yes
Height Adjustment	No

Display Tilt	+ 45 / - 45
Swivel / Pivot	+45 / - 45
Display Rotation	0

Physical Characteristics

Color	Black
Material	Aluminum
Product Length	4.5 in [11.5 cm]
Product Width	4.5 in [11.5 cm]
Product Height	2.1 in [5.4 cm]
Weight of Product	9.6 oz [272.0 g]

Packaging Information

Package Quantity	1
Package Length	4.9 in [12.4 cm]
Package Width	5.3 in [13.5 cm]
Package Height	2.5 in [6.4 cm]
Shipping (Package) Weight	14.9 oz [422.0 g]

What's in the Box

Included in Package	1 - display mount
	1 - hex key
	1 - wrench
	4 - M4x14 mm screws
	4 - M5x14 mm screws
	4 - washers
	2 - screws

2 - wall screws

1 - instruction manual

**Warranty
Information**

Warranty	5 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

