

3.3 ft (1m) USB-C to Mini DisplayPort Cable - 4K 60Hz - Black

Product ID: CDP2MDPMM1MB



This USB-C to Mini DisplayPort cable lets you connect your Thunderbolt 3 or USB Type-C enabled device to a Mini DP monitor with just one cable, for a convenient, clutter-free connection.

Harness the video capabilities that are built into your USB-C connection. The USB Type-C to Mini DisplayPort cable delivers the astonishing quality of Ultra HD to your 4K display, at resolutions up to 3840 x 2160. Plus, the adapter is backward compatible with 1080p displays, which makes it a great accessory for home, office or other work environments.

At 1 m (3.3 ft.) in length, this Mini DP cable delivers a compact connection that eliminates excess adapters and cabling, ensuring a tidy, professional installation. For longer installations, we also offer a 6 ft. (1.8 m) USB-C to mDP cable, enabling you to choose the right cable length for your custom installation needs.

For easy operation and installation, this USB 3.1 Type-C to Mini DP adapter cable supports plug-and-play installation on both Windows and Mac computers.

CDP2MDPMM1MB is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect your MacBook or USB-C device to an mDP monitor
- Ideal for home office or hot desk environments

- Experience crisp visuals with support for 4K 60Hz
- Deliver enriched presentations on the go

Features

- **ADAPTER AND CABLE IN ONE:** This USB-C to Mini DP cable lets you connect your Thunderbolt 3, Thunderbolt 4 or USB-C computer to a Mini DisplayPort (mDP) monitor with just one cable
- **NOTE:** This is not a Thunderbolt cable, not reversible and is not compatible with Thunderbolt peripherals such as Docking Stations, Displays or External Enclosures; This cable connects a USB-C or Thunderbolt 3/4 laptop to a monitor with Mini-DisplayPort
- **4K 60HZ RESOLUTION:** USB-C to Mini DisplayPort Cable Adapter delivers UHD picture quality with support for video resolutions up to 4K 60Hz; It's also backwards compatible with 1080p monitors or displays
- **HASSLE-FREE SETUP:** This USB Type-C to Mini DP adapter cable supports plug-and-play installation on both Windows and Mac computers; No driver installation required
- **THUNDERBOLT 3 AND USB-C COMPATIBLE:** USB-C to mDP cable works with Thunderbolt 3 / 4 computers and USB Type-C ports supporting video; Please check with your computer manufacturer to confirm video over USB-C (DP Alt mode) support

Hardware

Warranty	3 Years
AV Input	USB-C
Ports	1
AV Output	Mini DisplayPort - 1.2
Chipset ID	STMicroelectronics - STM32F072CBU6

Performance

Maximum Digital Resolutions	3840x2160 @ 60 Hz
Supported Resolutions	1024x7681280x720 (High-definition 720p)1920x1080 (High-definition 1080p)1920x12002560x14402560x16003840x2160 (Ultra HD 4K)
Wide Screen Supported	Yes
Audio Specifications	DisplayPort - 5.1 Channel Audio

Connector(s)

Connector A	1 - USB-C (24 pin) DisplayPort Alt Mode
-------------	---

Connector B 1 - Mini-DisplayPort (20 pin)

Special Notes / Requirements

Note	Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter.
------	---

Environmental

Operating Temperature	5C to 35C (41F to 95F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	25%-60%RH

Physical Characteristics

Color	Black
Cable Length	3.3 ft [1 m]
Product Length	3.3 ft [1.0 m]
Product Width	0.8 in [2.0 cm]
Product Height	0.4 in [1.0 cm]
Weight of Product	1.1 oz [32.0 g]

Packaging Information

Package Quantity	1
Package Length	6.3 in [15.9 cm]
Package Width	5.0 in [12.8 cm]
Package Height	1.0 in [2.5 cm]
Shipping (Package) Weight	1.4 oz [40.0 g]

What's in the Box

Included in Package	1 - USB-C to Mini DisplayPort cable
---------------------	-------------------------------------

Warranty Information

Warranty	3 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***

