

USB C Multiport Adapter - USB-C to HDMI 2.0b 4K 60Hz (HDR10), 100W Power Delivery Pass-Through, 4-Port USB 3.0 Hub - USB Type-C Mini Dock - 12" (30cm) Long Attached Cable

Product ID: DKT30CHPD3



This USB-C multiport adapter with DP 1.4 supports 4K 60Hz HDMI and turns your MacBook Pro, Dell XPS, or other USB-C laptops or tablet into a workstation, anywhere you go. The USB Type-C multiport adapter provides 4K HDMI video output, three USB 3.2 Gen 1 Type-A (5Gbps) ports including one BC 1.2 charge port; one USB-C port supporting both the 100W PD passthrough, all through one connection to your laptop's USB-C or Thunderbolt 3 port. Plus, it offers advanced charging through USB Power Delivery 3.0 and an extra-long attached 12-inch (30 cm) host cable for an extended reach to offer more set up flexibility.

The portable docking station connects your laptop to a 4K 60Hz HDMI monitor (4096 x 2160p) to create a powerful workstation. It can also connect to an ultrawide monitor.

The USB-C to USB 3.1 Gen 1 hub gives you three USB-A ports to connect your legacy USB devices, plus one shared USB-C port for either power delivery pass through.

With support for USB PD 3.0 (up to 100W), the USB Type-C multiport adapter lets you power and charge your laptop, and power your peripherals when connected to a USB-C power adapter. PD 3.0 features Fast Role Swap to prevent USB data disruption when you switch power sources (USB-C power adapter to bus power).

The DKT30CHPD3 is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Note: To ensure full adapter functionality, your laptop's USB-C port must support USB Power Delivery.

Certifications, Reports and Compatibility





Applications

Features

- **5-IN-1 MULTIPORT ADAPTER:** USB-C multiport adapter with DP 1.4 Alt-Mode up to 4K 60Hz (4K 30Hz with DP 1.2) HDMI 2.0b (HDR10) video; 4-Port USB Hub 5Gbps: 3x USB-A (USB 3.2/3.1 Gen 1) with 1x BC 1.2 charging, 1x USB-C (100W PD Passthrough)
- **EXTRA LONG CABLE:** USB C to HDMI multiport adapter with 12" (30cm) attached cable for extended reach to reduce port/connector strain on 2-in-1 devices like Surface Pro 7, iPad Pro, HP Elite x2 & laptops on riser stands
- **PORTABLE & COMPACT:** Portable all-in-one USB Type-C multiport adapter is made from durable aluminum & designed for easy transport in a laptop bag for convenient on-the-go use between office, home office, shared office spaces, and business travel
- **RELIABLE PERFORMANCE:** USB bus powered or via external USB-C power adapter; 100W Power Delivery 3.0 pass through w/ 12W reserved for adapter to avoid video flickering, device dropouts or overdrawing power common in other hubs; up to 88W for laptop charging
- **WIDE COMPATIBILITY:** Compatible with USB-C laptops, ultrabooks & Chromebooks, plus Thunderbolt 3 laptops from HP, Dell, Lenovo, MacBooks (Intel processor & M1 chip), and Surface Laptop 4; USBC mini dock works w/ Windows, macOS, iPadOS, Android & Chrome OS
- **4K 60HZ WITH DP 1.4 ALT-MODE:** Supports 4K 60Hz on host devices that support DP 1.4 Alt-Mode (min. Intel 11th Gen); on host devices that support DP 1.2 Alt-Mode, maximum video output resolution is 4K 30Hz; works w/ ultra-wide monitors up to 3440x1440@60Hz

Hardware

Warranty	3 Years
4K Support	Yes
Fast-Charge Port(s)	No
Displays Supported	1
Interface	USB 3.2 Gen 1
Bus Type	USB-C

Industry Standards USB 3.0 - Backward compatible with USB 2.0 and 1.1

Chipset ID Parade Technologies - PS176

VIA Tech - VL102

VIA Tech - VL817

Performance

Maximum Data Transfer Rate 5 Gbps (USB 3.1) Gen 1

Maximum Digital Resolutions 4K @ 60Hz (on hosts that support DP 1.4), 4K @ 30Hz (on hosts that support DP 1.2)

Type and Rate USB 3.0 - 5 Gbit/s

UASP Support Yes

Connector(s)

Connector Type(s) 1 - HDMI (19 pin)

3 - USB Type-A (9 pin, 5 Gbps)

1 - USB Type-C (24 pin) USB Power Delivery Only

Host Connectors 1 - USB 3.2 Type-C (24 pin, Gen 1, 5Gbps)

Software

OS Compatibility Windows 7, 8, 8.1, 10, 11, 11 ARM
macOS 10.9 to 10.15, 11.0, 12.0, 13.0, 14.0, 15.0, 26.1
Chrome OS

Power

Power Source Bus Powered and Host USB-C Power Adapter

Power Delivery 100W

Output Voltage 5 DC

Environmental

Operating Temperature 0 to +45

Storage Temperature -10 to +70

Humidity 10% to 90 % RH

Physical Characteristics

Color	Black & Gray
Material	Plastic
Cable Length	11.8 in [30 cm]
Product Length	1.3 in [3.4 cm]
Product Width	5.9 in [15.0 cm]
Product Height	0.4 in [1.1 cm]
Weight of Product	2.2 oz [61.0 g]

Packaging Information

Package Quantity	1
Package Length	5.6 in [14.3 cm]
Package Width	6.8 in [17.2 cm]
Package Height	1.3 in [3.4 cm]
Shipping (Package) Weight	4.2 oz [118.0 g]

What's in the Box

Included in Package	1 - USB-C Multiport Adapter
	1 - Product Documentation

Warranty Information

Warranty	3 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

