

DisplayPort to VGA Adapter - Active DP to VGA Converter - 1080p Video - Durable - DP/DP++  
Source to VGA Monitor Cable Adapter Dongle - DP 1.2 to VGA - Latching DP Connector

**Product ID:** DP2VGA



The StarTech.com DP2VGA DisplayPort to VGA adapter lets you connect a VGA computer monitor to a DisplayPort video card or other DisplayPort source, eliminating the expense of upgrading the monitor for compatibility.

The DP to VGA adapter uses an integrated chip to provide an active digital to analog conversion.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Keep your existing VGA monitor to be used with your new DisplayPort PC
- Ideal for using your VGA monitor as a secondary display

## Features

- **DISPLAYPORT TO VGA ADAPTER:** DisplayPort 1.2 (HBR2) adapter connects a VGA display or projector supporting 2048x1280, 1920x1200 & 1920x1080 (1080p) at 60Hz; EDID & DDC pass-through ensure compatibility between source & display 3" (8cm) attached cable

- **COMPATIBILITY:** Active digital to analog converter supports DP or DP++ source w/ standard DP connector incl workstations, desktops (AMD/Nvidia), laptops, small form factor computers & docking stations
- **CONNECT TO A PRIMARY OR SECONDARY DISPLAY:** Connect a VGA monitor or projector, or add a second display to your workstation using the DP to VGA display adapter; Durable housing makes it ideal for travel to & from office/home Tested w/ VGA cables up to 25'
- **LATCHING DISPLAYPORT & SCREW LOCKING VGA:** Latching DP connector ensures a solid host connection Supports VGA screw locking cable to prevent cable from coming loose or accidental disconnection EMI shielding protects from line noise/distortion
- **EASY TO USE:** With no software or drivers required, the DP to VGA adapter converter works with any OS including Windows, Ubuntu and macOS; DisplayPort male to VGA female video adapter dongle

---

#### Hardware

Warranty	3 Years
Active or Passive Adapter	Active
AV Input	DisplayPort - 1.2
AV Output	VGA
Audio	No

---

#### Performance

Maximum Analog Resolutions	1920x1200
Wide Screen Supported	Yes
Audio Specifications	VGA - No Audio Support

---

#### Connector(s)

Connector A	1 - DisplayPort (20 pin)
Connector B	1 - VGA (15 pin, High Density D-Sub)

---

#### Environmental

Operating Temperature	0°C (32°F) to 40°C (104°F)
Storage Temperature	-20°C (-4°F) to 60°C (140°F)
Humidity	20 - 90%

---

#### Physical Characteristics

Color	Black
-------	-------

---

Material	Plastic
Cable Length	3.0 in [77 mm]
Product Length	8.0 in [20.3 cm]
Product Width	1.5 in [3.8 cm]
Product Height	0.9 in [2.2 cm]
Weight of Product	2.4 oz [68.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	4.6 in [11.6 cm]
Package Width	7.8 in [19.8 cm]
Package Height	1.0 in [2.5 cm]
Shipping (Package) Weight	2.5 oz [72.0 g]

---

**What's in the Box**

Included in Package	1 - DisplayPort to VGA Adapter
---------------------	--------------------------------

---

**Warranty Information**

Warranty	3 Years
----------	---------

---

*\*Product appearance and specifications are subject to change without notice.*

