

1 ft DVI-D to 2x DVI-D Digital Video Splitter Cable - M/F

Product ID: DVISPL1DD



The DVISPL1DD 1ft DVI-D Splitter Cable lets you connect two DVI-D displays, or projectors to a single DVI-D digital video output port on your computer.

Backed by StarTech.com's lifetime warranty, the DVISPL1DD is a reliable and cost-effective solution for dual DVI monitor configurations.

Certifications, Reports and Compatibility



Applications

- Output one DVI digital video signal to two DVI-D displays simultaneously
- Ideal for use LCD TV, LCD Projectors, Plasma TV, HDTV and DVD Player and set-top box

Features

- **DVI SPLITTER FOR MIRRORED DISPLAYS:** View two identical DVI-Digital (24-pin) images from a single DVI-Digital (24-pin) source with this 1ft (30cm) DVI-D to 2x DVI-D (DVI-Digital) splitter; DVI-Analog signal is not supported
- **PERFORMANCE & RELIABILITY:** This DVI-D male to 2x DVI-D female splitter offers a built-in 12" cable to remove strain from the DVI-Digital source connector; we recommend DVI-D cables (DVIDDMM6) for high performance & signal reliability

- **FULL HD SPLITTER:** This cable is best suited for PCs that have a graphics card w/ DVI output, and may not work w/ adapters that convert HDMI/DP/USBC to DVI, or docking stations; This is a passive adapter and resolutions over 1920x1200 are not recommended
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this DVI-D video splitter is backed for life, including free lifetime 24/5 multi-lingual technical assistance
- **NOTE:** Splitter delivers two identical images of the same resolution; cannot be used to span an image across displays or to show different images on each display; product will display the same image on two monitors

Hardware

Warranty	Lifetime
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Maximum Digital Resolutions	2560 1600 @ 60Hz
-----------------------------	------------------

Connector(s)

Connector A	1 - DVI-D (25 pin)
Connector B	2 - DVI-D (25 pin)

Special Notes / Requirements

Note	This product will split your video signal to deliver two identical images of the same resolution. It cannot be used to span an image across two displays, or to show different images on each display.
------	--

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	1.0 ft [0.3 m]
Product Length	12.0 in [30.5 cm]
Product Width	1.7 in [4.2 cm]
Product Height	1.5 in [3.7 cm]

Weight of Product	5.4 oz [153 g]
-------------------	----------------

Packaging Information

Package Quantity	1
Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	1.5 in [39 mm]
Shipping (Package) Weight	5.6 oz [158 g]

What's in the Box

Included in Package	1 - 1 ft DVI-D to 2x DVI-D Digital Video Splitter Cable - M/F
---------------------	---

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*