

## 2m 3.5mm 4 Position TRRS Headset Extension Cable - M/F

**Product ID:** MUHSMF2M



The MUHSMF2M 4-Pole 3.5mm headset extension cable (2m) features a 3.5mm (1/8" TRRS) audio connector on one end and a 3.5mm (1/8" TRRS) audio connector on the other, making it easy to extend the reach between your hands-free headset or headphones, and your iPhone, mobile phone or laptop computer.

To ensure long-lasting performance, this high quality 3.5mm audio extension cable features molded PVC strain relief at each of the 1/8" TRRS connectors, which prevents the cable termination points from bending at sharp angles, in turn reducing the risk of cable damage.

**< b >Please note:< /b >**

To ensure proper hardware detection, we recommend that the external headset be plugged into the adapter first, before the adapter is connected to the computer or mobile device.

Also, in some circumstances, when an extension cable is used with an in-line remote control equipped headset, the remote control functions may not operate properly. This is due to the sensitivity of the remote control circuitry and does not indicate any defect in the cable.

## Certifications, Reports and Compatibility



## Applications

- Extend the reach between your hands-free headset and an iPhone or other mobile phone
- Add connection distance between your headset and your laptop or desktop computer audio port

## Features

- 4-pole 3.5mm connectors with molded PVC strain relief

---

### Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride

---

### Connector(s)

Connector A	1 - 3.5 mm Mini-Jack (4 Position)
Connector B	2 - 3.5 mm Mini-Jack (4 Position)

---

### Special Notes / Requirements

Note	3.5 mm Mini-Jack (4 position) male is configured per CTIA Standard
------	--------------------------------------------------------------------

---

### Environmental

Operating Temperature	-20C to 80C (-4F to 176F)
Storage Temperature	-20C to 80C (-4F to 176F)
Humidity	40% ~ 60%RH

---

### Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	6.6 ft [2 m]
Product Length	6.6 ft [2.0 m]
Product Width	0.2 in [0.6 cm]
Product Height	2.8 in [7.0 cm]
Weight of Product	1.3 oz [37.0 g]

---

### Packaging

**Information**

Package Quantity	1
Package Length	5.5 in [14.0 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.6 in [1.4 cm]
Shipping (Package) Weight	1.7 oz [48.0 g]

---

**What's in the Box**

Included in Package	1 - 2m 3.5mm 4 Position Headset Extension Cable - M/F
---------------------	-------------------------------------------------------

---

**Warranty Information**

Warranty	Lifetime
----------	----------

---

*\*Product appearance and specifications are subject to change without notice.*

