

6 foot (2m) Durable Black USB-A to Lightning Cable - Heavy Duty Rugged Aramid Fiber USB Type A to Lightning Charger/Sync Power Cord - Apple MFi Certified iPad/iPhone 12

Product ID: RUSBLTMM2MB



This USB to Lightning cable withstands the daily demands of charging and syncing your mobile devices. Tested to endure strenuous wear and tear and winter and summer in-car use, the rugged cable is a must-have for both business and consumer applications.

The durable Lightning cable has aramid fiber reinforcement that shelters it from the stress of frequent bends and twists. This also lets the cable flex without over-stretching, and strengthens the core of the cable.

Cable Key Features

- Aramid fiber adds strength and durability to the cable
- Insulated conductors reduce friction, provide more flexibility
- EMI (electromagnetic interference) protection with aluminum-mylar foil with braided shielding
- TPE (thermoplastic elastomer) cable jacket is softer and more flexible than a standard PVC cable and environmentally friendly

The cable is constructed to prevent the connector from separating from the jacket. The extra-long strain relief molding is tested to withstand over 10,000+ bend cycles at a 180 angle. Plus, the improved inner molding resists cracking and reduces cable damage.

Connector Key Features

- Lightning connector provides 12W for charging your iOS devices
- Metal shield protects circuit board from EMI and reinforces the connection point
- Strain relief tested to tolerate over 10,000+ bend cycles at a 180 angle

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to our customers. Our local StarTech.com Technical Advisors have a broad product expertise and work directly with StarTech.com Engineers to provide support for our customers both pre and post-sales.

RUSBLTMM2MB is an Apple MFi certified Lightning cable backed by a StarTech.com 2-year warranty.

Certifications, Reports and Compatibility



Applications

- Charge and sync your Lightning mobile devices

Features

- **DURABLE:** 6.6 ft. Heavy duty lightning cable with aramid fiber for high tensile strength increasing reliability & life of cable; Long lasting cable tested to withstand 10000+ bend cycles at 180 & 5000+ insertions
- **FLEXIBLE CABLE:** TPE jacket absorbs stress of frequent bends without damaging the core of the cable. Durable wire & connector protects this charge & sync cord from wear & tear of frequent in-car use
- **APPLE MFI CERTIFIED:** USB-A to lightning adapter cable for guaranteed fast & reliable charge/sync from USB Type-A charger port for lightning devices including iPhones Pro/Max/Mini/XR up to iPhone 14, iPad Air, iPad, iPad Mini
- **CHARGE LIGHTNING DEVICES:** Compatible with devices equipped with lightning port, incl AirPods, Magic Keyboard, Magic Trackpad, Magic Mouse and Siri Remote
- **CABLE SPECS:** Length: 2 m (6.6 ft.) Color: Black Connectors: Lightning & USB-A Performance: USB 2.0 480Mbps Reinforcement: Aramid Fiber Jacket Type: TPE Shield: Al-Mylar Backed by StarTech.com for 2 years

Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

Connector(s)		
	Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
	Connector B	1 - Apple Lightning Connector (8-pin)
Physical Characteristics		
	Color	Black
	Connector Style	Straight
	Wire Gauge	22/32 AWG
	Cable Length	6.6 ft [2 m]
	Product Length	6.6 ft [2.0 m]
	Product Width	0.6 in [1.5 cm]
	Product Height	0.2 in [0.5 cm]
	Weight of Product	1.6 oz [44.0 g]
Packaging Information		
	Package Quantity	1
	Package Length	3.0 in [7.6 cm]
	Package Width	7.3 in [18.5 cm]
	Package Height	1.2 in [3.0 cm]
	Shipping (Package) Weight	2.5 oz [70.0 g]
What's in the Box		
	Included in Package	1 - USB to Lightning cable
Warranty Information		
	Warranty	2 Years

**Product appearance and specifications are subject to change without notice.*