

ZCEA8

Limit switch head, Limit switches XC Standard,
ZCE, spring rod lever silicone boot





Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCE
Head type	Multi-directional head
Product Compatibility	XCMD XCKD XCKT XCKP

Associated body	ZCMD29L2 ZCP39 ZCMD25L1 ZCMD21C12 ZCMD25L5 ZCT26N12 ZCMD37L1 ZCT21N12 ZCP25 ZCD26 ZCT28P16 ZCP35 ZCD39 ZCMD39L2 ZCD25 ZCMD21L1 ZCT21P16 ZCD29M12 ZCP28 ZCMD21L5 ZCP27 ZCMD69C12 ZCT26G11 ZCD21M12 ZCT26P16 ZCT21G11 ZCMD21L08U78 ZCD21 ZCMD81L1 ZCP29M12 ZCMD29L1 ZCMD61C12 ZCMD41L2 ZCD37 ZCMD37L2 ZCT25G11 ZCD28 ZCMD41L1 ZCT28N12 ZCP31 ZCMD21M12 ZCP21 ZCT27N12 ZCMD39L5 ZCMD21L08R12 ZCMD81L5 ZCMD61M12 ZCT28G11 ZCT25P16 ZCP37 ZCMD37L5 ZCMD25L2 ZCD31 ZCMD41L5 ZCP26 ZCMD39L1 ZCP29 ZCMD81L2 ZCMD29C12 ZCT27G11 ZCMD21L2 ZCD27 ZCT25N12 ZCP21M12 ZCMD29L5 ZCD35 ZCT27P16 ZCD29
Movement of operating head	Multi-directional
Type of operator	Spring rod spring return metal with silicone boot)
Type of approach	Multi-directional approach

Complementary

Switch actuation	By any moving part
Positive opening	Without

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22413-LIMIT SWITCH, IEC, MINIATURE
Discount Schedule	T
GTIN	3389119023733
Returnability	No
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.67 in (1.7 cm)
Package 1 Width	1.57 in (4 cm)
Package 1 Length	5.12 in (13 cm)
Package 1 Weight	0.85 oz (24 g)
Unit Type of Package 2	BAG
Number of Units in Package 2	10
Package 2 Height	4.72 in (12 cm)
Package 2 Width	1.57 in (4 cm)
Package 2 Length	7.87 in (20 cm)
Package 2 Weight	10.23 oz (290 g)
Unit Type of Package 3	S01
Number of Units in Package 3	150
Package 3 Height	5.91 in (15 cm)
Package 3 Width	5.91 in (15 cm)
Package 3 Length	15.75 in (40 cm)
Package 3 Weight	8.43 lb(US) (3.825 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------