

USB 3.0 to Gigabit Ethernet Network Adapter, 10/100/1000 Mbps, USB to RJ45, USB 3.0 to LAN Adapter, USB 3.0 Ethernet Adapter (GbE), TAA Compliant

Product ID: USB31000S



The USB31000S USB 3.0 to Gigabit Ethernet Adapter adds a single RJ45 Ethernet port to a USB-enabled computer system, with support for Gigabit network connections at full bandwidth, unlike USB 2.0 adapters.

This compact USB 3.0 network adapter is backward compatible with older USB 2.0/1.x computer systems (speed limited by USB bus), making it the ideal portable replacement network adapter or laptop accessory. Plus, with support for features such as Jumbo Frames, VLAN tagging and Wake on LAN (WOL), the adapter offers a versatile Gigabit network solution for home and business users alike.

The USB31000S USB 3.0 Gigabit adapter is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Add Gigabit Ethernet capabilities to a desktop or laptop, without opening the computer or taking up an available expansion slot
- Replace a failed integrated network adapter with an external, USB Gigabit Ethernet connection, instead of having to open a desktop or laptop computer case
- Connects your laptop PC to a Gigabit network or backbone - perfect for small or home offices, departmental network applications and network gaming
- Transfer very large files over the network with access to true Gigabit speeds that USB 2.0 adapters cannot provide

Features

- **USB NETWORK ADAPTER:** USB to RJ45 adapter adds an Ethernet port to your computer supporting up to Gigabit speeds on 10/100/1000 Mbps Networks; Ideal for reliable wired gigabit network connections, or as an alternative to WiFi
- **FULL FEATURED:** USB to Ethernet dongle; Uses ASIX AX88179A Chipset for native compatibility with laptops and desktops, and 2-in-1's computers; USB Bus Powered; Status & Activity LED's indicators
- **OS COMPATIBILITY:** USB NIC adapter for laptop; Works with Windows versions 7 and up, Windows Server, macOS 10.14 and up, Ubuntu 20.04 Kernel 5.15 and up (LTS Versions only), and ChromeOS, TAA Compliant
- **TECHNICAL SPECS:** USB 3.2 Gen 1 Type-A (5 Gbps); Compatible with USB 3.0/2.0; 1x RJ45; 4K Jumbo Frames; VLAN Tagging; Wake on LAN; Energy Efficient Ethernet (EEE); Supports twisted pair crossover & auto detection (Auto-MDIX); Color: Black
- **CONNECTIVITY TOOLS:** Provided with this device, the application improves performance and security, featuring MAC Address Changer & Wi-Fi Auto Switch utilities

Hardware

Warranty	2 Years
Ports	1
Interface	RJ45 (Gigabit Ethernet)
Bus Type	USB 3.2 Gen 1 (5Gbps)
Industry Standards	IEEE802.3i, IEEE 802.3u, IEEE 802.3ab, IEEE 802.3az, IEEE 802.1q VLAN tagging
Chipset ID	ASIX - AX88179A

Performance

Wake On Lan	Yes
Max Distance	100m [328ft]

Type and Rate	USB 3.0 - 5 Gbit/s
Compatible Networks	10/100/1000 Mbps
Auto MDIX	Yes
Full Duplex Support	Yes
Jumbo Frame Support	4K max.

Connector(s)

Connector Type(s)	1 - RJ-45
	1 - USB Type-A (9 pin, 5 Gbps)

Software

OS Compatibility	Windows XP, Vista, 7, 8, 8.1, 10, 11, 11 ARM
	Windows Server 2003, 2008 R2, 2012, 2012 R2, 2016, 2019, 2022, 2025
	macOS 10.6 to 10.15, 11.3 to 26.1 VLAN tagging is currently not supported in macOS
	Ubuntu 20.04 Kernel 5.15 and up - LTS Versions only
	ChromeOS 55+

Special Notes / Requirements

System and Cable Requirements	Available USB port
Note	Jumbo Frames are no longer supported in macOS

Indicators

LED Indicators	1 - Link (Amber)
	1 - Activity (Green)

Power

Power Source	USB-Powered
Input Voltage	5V DC
Output Voltage	5 DC

Environmental

Operating Temperature	0C to 40C (32F to 104F)
-----------------------	-------------------------

Storage Temperature -20C to 60C (-4F to 140F)

Humidity < 80% RH

Physical Characteristics

Color	Black
Form Factor	Attached Cable
Material	Plastic
Cable Length	5.3 in [135 mm]
Product Length	8.5 in [21.5 cm]
Product Width	1.0 in [2.6 cm]
Product Height	0.6 in [1.6 cm]
Weight of Product	1.0 oz [28.0 g]

Packaging Information

Package Quantity	1
Package Length	6.9 in [17.6 cm]
Package Width	5.0 in [12.6 cm]
Package Height	0.7 in [1.8 cm]
Shipping (Package) Weight	1.4 oz [40.0 g]

What's in the Box

Included in Package	1 - USB 3.0 Gigabit Adapter
	1 - Instruction Manual

Warranty Information

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*