

USB 3.0 to HDMI Adapter, USB to HDMI Monitor Converter for Windows, 1080P (no support for macOS/ChromeOS/Linux) - TAA

Product ID: USB32HDES



The USB32HDES Slim USB 3.0 to HDMI Adapter turns a USB 3.0 port into an HDMI output with 1920x1200/1080p video support. The adapter minimizes clutter with a slim design that seamlessly blends with your video cable - an ideal space-saving solution for multi-monitor applications on Ultrabook, laptop, or desktop computers.

Functioning as an external graphics card, this USB to HDMI adapter provides a convenient way to add multi-monitor capability to a USB 3.0-enabled desktop or laptop computer (optimal performance from USB 3.0, backward compatible with USB 2.0).

To save space while travelling, this ultra-portable USB to HDMI adapter features a lightweight, small footprint design that fits easily in a laptop carrying bag.

Leveraging the high-bandwidth (5 Gbps) SuperSpeed USB 3.0 interface, the adapter delivers smooth, high-definition content to your HDMI display/projector. The adapter can be used to mirror your primary desktop, showing the same image on each display, or to extend your desktop to double your workspace and increase your productivity.

The USB32HDES is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Recommended System Requirements:

CPU: Quad Core 2.4GHz or Higher (i5 recommended)

RAM: 4GB or higher

USB 3.0 Port (Backwards compatible with USB 2.0)

Certifications, Reports and Compatibility



Applications

- Add a secondary HDMI display with full HD capability
- View large or multiple spreadsheets across several displays
- Use the adapter to connect your PC to your HDMI-equipped projector or display for viewing family pictures and movies
- Add multi-monitor capability to a single computer, to create engaging multimedia presentations
- Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other
- Run multiple applications on different screens - check your email on one display and search the web on the other

Features

- **COMPATIBILITY:** This adapter is only compatible with Windows and does not support macOS, ChromeOS or Linux; Works with all Windows X86/X64/ARM platforms: Intel, AMD, and Snapdragon X Copilot+ PC; Administrator rights are required to install the drivers
- **INCREASE YOUR PRODUCTIVITY:** USB to HDMI monitor adapter lets you extend your desktop by adding an HDMI monitor to your laptop or desktop computer; Ideal for your workstation setup in the office or working from home
- **TRAVEL FRIENDLY:** External video graphics card features a lightweight compact design and is USB bus-powered with no extra power supply required (USB Bus Powered)
- **PERFORMANCE:** USB 5Gbps to HDMI hub converter (1x USB-A male to 1x HDMI female connector) offers 1920x1200 (1080p) 60Hz Video, 2ch audio (through HDMI) and 2.4in (6cm) cable length
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this USB Type-A to HDMI adapter dongle is backed for 3-years, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	3 Years
AV Input	USB 3.2 Gen 1 (5Gbps)
AV Output	HDMI

Audio	Yes
USB Pass-Through	No
Memory	16MB
Chipset ID	Trigger - T6-688SL

Performance

Maximum Digital Resolutions	1920x1200/1080p
Supported Resolutions	Widescreen(16/32 bit): 1920x1200, 1920x1080, 1680x1050, 1600x900, 1440x900, 1360x768, 1280x800, 1280x768, 1280x720
	Standard(16/32 bit): 1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864, 1024x768, 800x600
Wide Screen Supported	Yes
Audio Specifications	2-Channel Stereo (48Khz)

Connector(s)

Connector A	1 - USB Type-A (9 pin, 5 Gbps)
Connector B	1 - HDMI (19 pin)

Software

OS Compatibility	Windows 11, 11 ARM Windows 10 (32/64) Windows 8 / 8.1 (32/64) Windows 7(32/64) Windows Vista (32/64) Windows XP (32/64)
Microsoft WHQL Certified	Yes

Special Notes / Requirements

System and Cable	System Processor: Quad Core 2.4GHz (i5 recommended)
------------------	---

Requirements

System Memory: 4GB

Note

Connect a maximum of five USB video adapters on a single computer. Support for multiple adapters will vary depending upon your system resources

This USB video adapter is not intended for graphical intensive applications, such as gaming

Power

Power Source USB-Powered

Environmental

Operating Temperature 0C to 50C (32F to 122F)

Storage Temperature -10C to 75C (14F to 167F)

Humidity < 85% non-condensing

Physical Characteristics

Color Black

Material Plastic

Cable Length 2.4 in [62 mm]

Product Length 7.5 in [19.0 cm]

Product Width 1.0 in [2.5 cm]

Product Height 0.5 in [1.2 cm]

Weight of Product 0.9 oz [25.0 g]

Packaging Information

Package Quantity 1

Package Length 5.7 in [14.6 cm]

Package Width 7.0 in [17.7 cm]

Package Height 1.3 in [3.4 cm]

Shipping (Package) Weight 4.9 oz [138.0 g]

What's in the Box

Included in Package	1 - Slim USB 3.0 Video Adapter
	1 - Driver CD
	1 - instruction manual

**Warranty
Information**

Warranty	3 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

