

Slim Micro USB 3.0 (5Gbps) Cable - M/M - Right-Angle Micro-USB - 0.5m (20in)

Product ID: USB3AU50CMRS



This slim, sturdy USB 3.2 Gen 1 (5 Gbps) cable, better known as a USB 3.0 cable, lets you position Micro-USB devices on your desk without the cable getting in the way. It's thinner and more flexible than standard cables, and features a right-angled Micro-USB connector that prevents awkward bends at the connection port.

Now you can arrange your desk according to what works best for you, without worrying about the cable bending awkwardly or straining too much to make a connection. This durable, lightweight cable is roughly half the thickness of a regular USB 3.2 Gen 1 cable, giving you the flexibility and freedom to place your devices as needed, with minimal clutter.

This versatile cable features a right-angled connector, which offers a more natural fit at the device connection point and helps prevent unnecessary strain and damage to the port. Plus, the short 0.5 m/1.5 ft. cable length makes this an excellent solution for close-range connections and portable applications such as connecting a portable hard drive to your laptop.

Charge your mobile device in your car or sync with your laptop.

As well as being ideal for connecting to your desktop devices, this cable provides the perfect solution for charging and syncing your USB 3.2 Gen 1 Micro B-equipped phones and tablets.

The short cable design is just right for people on the move, for providing simple, tidy connections and it fits nicely inside your laptop or tablet carrying case.

The cable features a thin, yet sturdy connector molding, so you'll be able to connect to your phone or tablet without removing its protective case. And, the cable's right-angled Micro-USB connector lets you text, work or game on your mobile device -- even while it's charging -- without the cable getting in the way.

The USB3AU50CMRS 0.5m cable is backed by StarTech.com's lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Connect Micro-USB 3.0 devices (portable hard drive, card reader, video capture device, hard drive enclosure, etc.) to a USB 3.0 compatible PC or laptop
- Charge and sync your USB 3.0 Micro B-equipped mobile digital devices

Features

- Position your USB 3.2 Gen1 devices as needed throughout your workspace
- Connect to your device even in hard-to-reach areas and tight spaces
- Portable design fits nicely into any carrying case
- Charge and sync your mobile devices without removing the protective case

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Type and Rate	USB 3.0 - 5 Gbit/s
---------------	--------------------

Connector(s)

Connector A	1 - USB Type-A (9 pin, 5 Gbps)
Connector B	1 - USB 3.0 Micro-B (10 pin, SuperSpeed)

Environmental

Operating Temperature	0°C (32°F) ~ 70°C (158°F)
Storage Temperature	-25°C (-13°F) ~ 85°C (185°F)
Humidity	20% ~ 90%

Physical Characteristics

Color	Black
Connector Style	Straight to Right Angle
Wire Gauge	26/32 AWG
Cable Length	1.6 ft [0.5 m]
Product Length	1.8 ft [0.5 m]
Product Width	0.0 in [0.0 cm]
Product Height	0.0 in [0.0 cm]
Weight of Product	0.8 oz [22.0 g]

Packaging Information

Package Quantity	1
Package Length	6.1 in [15.4 cm]
Package Width	7.8 in [19.9 cm]
Package Height	0.6 in [1.5 cm]
Shipping (Package) Weight	1.6 oz [44.0 g]

What's in the Box

Included in Package	1 - 0.5m Right-Angle Slim Micro-USB 3.0 Cable
---------------------	---

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***