


Short Micro-USB Cable - M/M - 1 ft

Product ID: USBAUB1BK



The USBAUB1BK Micro USB Cable is perfect for close-range connections, and provides a reliable solution for charging and syncing your Micro USB mobile devices. Plus, the cable offers a slim design that lets you plug into your device without having to take it out of its case for every charge and sync.

The short 1-foot cable length makes this an ideal charge cable for in-car use or to reduce clutter when syncing to your laptop - perfect for people on the move, for providing simple, tidy connections.

Replace the cable that came with your device and keep one as a spare in your laptop bag, backpack or other carrying case.

Stop removing the case from your phone or tablet every time you charge or sync your device. The cable offers a slim Micro USB connector molding that plugs into your device even while it's inside a protective case.

Designed and constructed for maximum durability, this high quality USB-A to Micro-B cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Charge and sync your Micro USB-equipped mobile digital devices

Features

- Slim Micro USB connector molding
- Aluminum-mylar foil with braided shielding
- Supports high-speed USB data transfer rates of up to 480 Mbps

Hardware

| | |
|-----------------------|--------------------------------|
| Warranty | Lifetime |
| Connector Plating | Nickel |
| Cable Jacket Material | PVC - Polyvinyl Chloride |
| Cable Shield Material | Aluminum-Mylar Foil with Braid |

Performance

| | |
|---------------|----------------------|
| Type and Rate | USB 2.0 - 480 Mbit/s |
|---------------|----------------------|

Connector(s)

| | |
|-------------|-------------------------------------|
| Connector A | 1 - USB 2.0 Type-A (4 pin, 480Mbps) |
| Connector B | 1 - USB Micro-B (5 pin) |

Special Notes / Requirements

| | |
|------|--|
| Note | Micro USB connector molding width is 10mm and height is 6mm (please see drawing) |
|------|--|

Physical Characteristics

| | |
|-------------------|-------------------|
| Color | Black |
| Connector Style | Straight |
| Wire Gauge | 28 AWG |
| Cable Length | 1.0 ft [0.3 m] |
| Product Length | 12.0 in [30.5 cm] |
| Product Width | 0.6 in [1.5 cm] |
| Product Height | 0.3 in [7.0 mm] |
| Weight of Product | 0.6 oz [18.3 g] |

**Packaging
Information**

| | |
|------------------------------|------------------|
| Package Quantity | 1 |
| Package Length | 5.2 in [13.2 cm] |
| Package Width | 5.0 in [12.8 cm] |
| Package Height | 0.4 in [1.1 cm] |
| Shipping (Package) Weight | 0.6 oz [18.0 g] |

What's in the Box

| | |
|---------------------|--|
| Included in Package | 1 - 1 ft Mobile Charge Sync Micro USB Cable - A to Micro B |
|---------------------|--|

**Warranty
Information**

| | |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

**Product appearance and specifications are subject to change without notice.*

