

TS 35X15/2.3 2M/CU/BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Copper has the best electrical conductivity of all metals used. The copper rail has the highest short-circuit protection.

General ordering data

Version	Terminal rail, Accessories, Copper, untreated, Width: 2000 mm, Height: 35 mm, Depth: 15 mm
Order No.	0270100000
Type	TS 35X15/2.3 2M/CU/BK
GTIN (EAN)	4008190105136
Qty.	20 m

TS 35X15/2.3 2M/CU/BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	15 mm	Depth (inches)	0.591 inch
Height	35 mm	Height (inches)	1.378 inch
Width	2,000 mm	Width (inches)	78.74 inch
Net weight	940 g		

Temperatures

Ambient temperature	-5 °C...40 °C
---------------------	---------------

Mounting rail

Installation advice	Direct mounting	
Length of the terminal rail	min.	0 mm
	max.	2,000 mm
	nominal	2,000 mm
Material	Copper	
Permitted thermal current for PEN function, max.	309 A	
Pre-punched mounting rail	No	
Short circuit strength corresponds to E-Cu wire	150 mm²	
Short-time withstand current per second according to IEC 60947-7-2	18 kA	
Slit gap		
Slit length		
Slit width		
Spacing of holes, centre-to-centre	0 mm	
Standards	DIN EN 60715	
Surface finish	untreated	
Thickness	2.3 mm	

Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 9.0	27-40-06-02
ECLASS 9.1	27-40-06-02	ECLASS 10.0	27-40-06-02
ECLASS 11.0	27-40-06-02	ECLASS 12.0	27-40-06-02
ECLASS 13.0	27-40-06-02	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

TS 35X15/2.3 2M/CU/BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	

TS 35X15/2.3 2M/CU/BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

