

2-Post Racks



L-Com's Floor Mount Steel Racks are perfect for mounting your networking equipment and panels in space constrained situations. Ideal for setup on any desktop/table top environment they can also be mounted on the floor as well. Made from high quality materials this product is made to industry specifications, ensuring compatability with your equipment.

| Model / SKU Number | | LC-2POST-25U-M6 | LC-2POST-45U-M6 | LC-2POST-02-22U | LC-2POST-02-42U | LC-2POST-13UAL-12-24 | LC-2POST-25UAL-12-24 | LC-2POST-45UAL-12-24 |
|-------------------------------|----------------------|---|---|---|---|--|--|--|
| PHYSICAL | | | | | | | | |
| Rack Capacity (in Rack Units) | | 25U | 45U | 22U | 42U | 13U | 25U | 45U |
| Unit Dimensions (in) | Н | 49 | 84 | 47 | 81.75 | 28 | 49 | 84 |
| | W | 20 | 20 | 23.5 | 23.5 | 20.25 | 20.25 | 20.25 |
| | D | 14.3 | 14.3 | 23.75 | 23.75 | 13.4 | 13.4 | 13.4 |
| Weight Capacity (kg / lbs) | | 400/881 | 400/881 | 150/330 | 150/330 | 300/661 | 300/661 | 300/661 |
| Material | | Cold Rolled Steel | | | | Aluminum | | |
| Painting / Coating | Black Powder Coating | | | | | | | |
| Construction | | Bolted Assembly | | | | | | |
| Rack Hole Type | | Square Holes | | | | Threaded (12-24) | | |
| ADDITIONAL FEATURES | | | | | | | | |
| Casters / Floor Mount | | Floor Mount (Compatible with Casters) | Floor Mount (Compatible with Casters) | Includes Casters (Can also Floor Mount) | Includes Casters (Can also Floor Mount) | Floor Mount (Compatible with Casters) | Floor Mount (Compatible with Casters) | Floor Mount (Compatible with Casters) |
| Cable Management | | Includes Cable Hooks | Includes Cable Hooks | Includes Cable Hooks | Available to Purchase | Includes Cable Hooks | Includes Cable Hooks | Includes Cable Hooks |
| Equipment Mounting Hardware | | (20 Sets) M6 Cage Nuts, Screws, Plastic Washers | (40 Sets) M6 Cage Nuts, Screws, Plastic Washers | (20 Sets) M6 Cage Nuts, Screws, Plastic Washers | (40 Sets) M6 Cage Nuts, Screws, Plastic Washers | (28 Sets) 12-24 Screws | (28 Sets) 12-24 Screws | (28 Sets) 12-24 Screws |
| Assembly | | Assembly Required | | | | | | |
| COMPLIANCE AND CERTIFICATIONS | | | | | | | | |
| EIA/ECA-310-E | | · | | | | | | |
| ROHS | | 4 | | | | | | |
| CE | | 4 | | | | | | |
| DIN 41494 | | 4 | | | | | | |
| IEC-60297-3-100 | | · | | | | | | |
| SHIPPING | | | | | | | | |
| Shipping Dimensions (in) | L | 51.2 | 86.2 | 60.6 | 80.1 | 30.3 | 51.2 | 85 |
| | W | 6.7 | 6.7 | 6.3 | 6.3 | 5.91 | 5.91 | 5.91 |
| | Н | 5.51 | 5.51 | 5.71 | 5.71 | 4.92 | 4.92 | 5.12 |
| Shipping Weight (lbs) | | 33.85 | 44 | 36.8 | 36.8 | 22.5 | 26.5 | 32.95 |