

TS 15X5 2M/ST/ZN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

Version	Terminal rail, Accessories, Steel, galvanic zinc plated and passivated, Width: 2000 mm, Height: 15 mm, Depth: 5.5 mm
Order No.	0514200000
Type	TS 15X5 2M/ST/ZN
GTIN (EAN)	4008190172428
Qty.	2 m

TS 15X5 2M/ST/ZN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	5.5 mm	Depth (inches)	0.217 inch
Height	15 mm	Height (inches)	0.591 inch
Width	2,000 mm	Width (inches)	78.74 inch
Net weight	155.5 g		

Temperatures

Ambient temperature	-5 °C...40 °C
---------------------	---------------

Mounting rail

Installation advice	Direct mounting		
Length of the terminal rail	nominal	2,000 mm	
	max.	2,000 mm	
	min.	0 mm	
Material	Steel		
Pre-punched mounting rail	No		
Short circuit strength corresponds to E-Cu wire	10 mm ²		
Short-time withstand current per second according to IEC 60947-7-2	1.2 kA		
Slit gap			
Slit length			
Slit width			
Spacing of holes, centre-to-centre	0 mm		
Standards	DIN EN 60715		
Surface finish	galvanic zinc plated and passivated		
Thickness	1 mm		

Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 9.0	27-40-06-02
ECLASS 9.1	27-40-06-02	ECLASS 10.0	27-40-06-02
ECLASS 11.0	27-40-06-02	ECLASS 12.0	27-40-06-02
ECLASS 13.0	27-40-06-02	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	

Creation date June 12, 2025 3:41:11 PM CEST

Catalogue status 07.06.2025 / We reserve the right to make technical changes.

TS 15X5 2M/ST/ZN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

