



SMA Male to RP TNC Female Adapter

SMA male to RP TNC female adapter part number SM5805 from Fairview Microwave is in-stock and ships same day. This Fairview SMA to reverse polarity TNC adapter has a male to female gender configuration. SM5805 SMA male to reverse polarity TNC female adapter operates to 11 GHz. The SMA connector mates mechanically with commercially available 3.5mm and 2.92mm (K) connectors. The Fairview Microwave RF adapter provides excellent VSWR of 1.25:1 maximum.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connnector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Min	Тур	Max	Units		
DC		11	GHz		
		1.25:1			
		-74	DC 11		

Electrical Specification Notes: Values at 25°C, sea level.

Mechanical Specifications

Size
Lengt
\\/idth

1.16 in [29.46 mm] 0.5 in [12.7 mm] 0.02646 lbs [12 q] Weight

Description	Connector 1	Connector 2
Туре	SMA Male	TNC Female
Polarity	Standard	Reverse Polarity
Interface Specification	MIL-STD-348	MIL-STD-348
Mating Cycles	500	500



Configuration:

- SMA Male Connector 1
- TNC Female Reverse Polarity Connector 2
- 50 Ohms
- Straight Body Geometry

Features:

- VSWR of 1.25:1 max up to 11 GHz
- SMA interface meets MIL-STD-348
- TNC interface meets MIL-STD-348
- · Contact plating according to MIL-G-45204
- Gold Plated Beryllium Copper Contact

Applications:

- · Enables Between Series Connections
- General Purpose Test

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Material Specifications

Description	Connector 1	Connector 1 Connector 2			
Туре	SMA Male	TNC Female			
Contact Material	Beryllium Copper	Beryllium Copper			
Contact Plating	Gold	Gold			
Contact Plating Spec.	MIL-G-45204	MIL-G-45204			
Insulation Material	PTFE	PTFE			
Outer Contact Material		Brass			
Outer Contact Plating		Nickel			
Outer Conductor Contact Spec	C.	QQ-N-290			
Body Material	Brass				
Body Plating	Nickel				
Body Plating Spec.	QQ-N-290				
Coupling Nut Material	Brass				
Coupling Nut Plating	Nickel				
Coupling Nut Plating Spec.	QQ-N-290				

Environmental Specifications

Temperature

Operating Range


-65 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data







SMA Male to RP TNC Female Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order


For additional information on this product, please click the following link: SMA Male to RP TNC Female Adapter SM5805

URL: https://www.fairviewmicrowave.com/sma-male-rp-tnc-female-adapter-sm5805-p.aspx

	nent improv												
stated, al	l specificati	ons are i	nominal.	Fairvie	w Microwa	ve does n	ot make	any rep	resentat	ion or v	warranty re	gard	ing the
suitability	of the part	t describ	ed hereir	for any	/ particulai	purpose,	and Fair	view Mi	crowave	does n	ot assume	any	liability
arising ou	t of the use	of any p	part or do	cument	ation.								







STANDARD TOLERANCES

X ±0.2 XX ±0.1 XXX ±0.05

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
SMA Male to RP TNC Female Adapter	DWG NO CAGE CODE SM5805					3FKR5	
	CAD FILE 100716	SHEET	SCALE	N/A	SIZE A	41742	