

Desk Mount Monitor Arm with 2x USB 3.0 Ports, Full Motion Single Monitor Mount, up to 34" (17.6lb/8kg) VESA Display, Clamp/Grommet Mount, Mechanical Spring

Product ID: ARMPIVOT2USB3



Save space with this premium desk mount monitor arm, by suspending your screen above your desk.

Use the single arm monitor mount to mount your VESA mount monitor (75x75, 100x100) up to 34".

Made of aluminum, the VESA mount monitor stand provides stable support for your display, with a weight capacity of up to 17.6 lb. (8 kg). Built-in USB 3.0 ports provide convenient connectivity for your computer.

The arm extends 20.2" (514 mm) to allow a wide range of motion. Move the monitor holder arm effortlessly side to side to adjust your screen.

With its articulating arm, the monitor mount makes it easy to find the right viewing angle. Pan +90/-90 degrees left or right and tilt your display +90/-90 degrees up or down. For landscape or portrait viewing, rotate your display +90/-90 degrees.

Work in comfort with this height adjustable monitor stand that lets you raise or lower the monitor arm along the pole, up to 24.4" (620 mm).

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales

The ARMPIVOT2USB3 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Mount your VESA mount display to the side of your desk or table in commercial, industrial or office setting
- Use the grommet or c-clamp to mount your display to your desk in a cubicle to save space
- Create a more ergonomic work-space in a business or home office

Features

- HEAVY DUTY MONITOR MOUNT: VESA 75x75/100x100mm compatible articulating desk mount monitor arm supports 1 large display up to 32" (16:9) or an ultrawide display up to 34" (21:9) up to 17.6lb (8kg); Full motion articulation; 2x USB 3.0 passthrough ports
- EASY INSTALLATION: Tighten c-clamp from top with incl. tool or grommet mount to secure to desk (0.4"-2"/10mm-50mm thick); Easily mount display with detachable VESA plate; tools incl. to adjust articulation tension
- MECHANICAL SPRING ONE-TOUCH ADJUSTMENT: Single monitor mount with mechanical spring arm allows a max height of 24.4in (62cm) from the desk, toolless 10" (25.4cm) height adjustability and outward extension up to 18.4in (46.7cm)
- WIDE RANGE OF MOTION: Ergonomic monitor arm increases comfort & productivity w/ +/-90 tilt, +/-90 swivel, 90 rotating screen (landscape/portrait) & toolless adjustable height along 11.8" (300mm) pole
- CONVENIENT CONNECTIVITY: This desk clamp monitor arm with USB includes 2x 5Gbps USB 3.2 Gen 1 passthrough ports that extend your PC/laptop/desktop computer/dock ports for connecting devices & built-in cable management

Hardware

Warranty	2 Years
Wallmountable	No
Articulating	Yes
# of Displays Supported	1
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	75x75 mm
	100x100 mm
Mounting Surface	Desk Clamp: Table Thickness 0.39 - 1.97 in. (10 - 50 mm)

Thickness

Grommet Clamp: Table Thickness 0.39 - 1.97 in. (10 - 50 mm)

Performance

Weight Capacity (Per Display)	17.6 lb [8 kg]
Minimum Display Size	17"
Maximum Display Size	34"
Height Adjustment	Yes
Maximum Height	24.4 in [620 mm]
Maximum Arm Extension	20.2 in [514 mm]
Display Tilt	+90 / - 90
Display Swivel	+90 / - 90
Swivel / Pivot	+/- 90 around the support post +/- 180 at the shoulder +/- 90 at the elbow
Display Rotation	+90 / - 90

Physical Characteristics

Color	Black
Material	Aluminum
Product Length	23.4 in [59.4 cm]
Product Width	1.4 in [3.5 cm]
Product Height	24.4 in [62.0 cm]
Weight of Product	7.2 lb [3.2 kg]

Packaging Information

Package Quantity	1
Package Length	9.8 in [24.8 cm]
Package Width	17.4 in [44.1 cm]

Package Height 4.9 in [12.4 cm]

Shipping (Package) Weight 9.2 lb [4.2 kg]

What's in the Box

Included in Package	1 - Base Assembly
	1 - Lower Arm
	1 - Upper Arm
	1 - Pole
	1 - VESA Plate
	1 - Arm Shoulder
	1 - Tool Holder
	1 - Cable Management Clip
	1 - Grommet Plate
	1 - Grommet Screw
	1 - 3mm Hex Key
	1 - 6mm Hex Key
	4 - M4 x 12mm Screws
	4 - M5 x 12mm Screws
	4 - Washers

Warranty Information

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***