

USB-C to VGA Adapter - 1920x1200 - TAA

Product ID: CDP2VGASA



This is no ordinary video adapter. Yes, it enables you to connect the USB-C port on your computer to a VGA display or projector, but it also features a unique Presentation Mode switch. When you turn on this switch, the adapter prevents your computer from launching its screen saver, going to sleep or entering power save mode. The adapter ensures that your screen will always stay on, making it the perfect USB-C video adapter for any presentation or meeting.

When you deliver a presentation, your goal is to engage with your audience, not your computer. But, if you don't move your mouse soon enough, or change your power settings, your screen goes black due to inactivity while you're addressing the audience. This can be a major distraction when you're trying to focus on the message you're communicating.

This adapter prevents screen disruptions with Presentation Mode, a unique feature that automatically initiates occasional cursor movement to prevent your computer's power settings from interrupting your presentation. It's perfect for sharing websites, drawings, spreadsheets, PDFs or slide shows during your meeting.

You can turn Presentation Mode on or off, depending on your application. Turn it on when you're in the boardroom and want your screen to stay on, and turn it off when you're using the adapter at your workspace or office desk, to enable your computer's original power settings to take effect. Using the toggle switch is easy, and saves you the hassle of constantly making adjustments in your operating system settings.

To ensure easy operation and installation, this unique adapter is natively supported on Windows and Mac computers. It's easy to connect the adapter using the versatile USB Type-C port on your computer. The reversible USB-C connector means you will always plug it in correctly on your first try, saving you the hassle and distraction of repeatedly attempting to connect your laptop to a display or projector.

The adapter supports video resolutions up to 1920x1200 or 1080p. You'll be surprised at the picture quality the adapter provides, even when you connect it to a legacy VGA projector or television. The adapter harnesses the video capabilities that are built into your USB Type-C connection to deliver every detail in stunning high-definition.

The CDP2VGASA is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Be ready to present from your laptop, with the peace of mind in knowing your laptop won't enter power save mode when you don't want it to
- Keep this adapter with you while you travel to ensure you can connect to any VGA display you come across
- Connect a VGA display to your USB-C laptop to use as a secondary monitor

Features

- Equipped with a Presentation Mode feature to ensure your video output is not interrupted by your computer's power saving modes
- Avoid the hassle of adjusting power settings, with an easy-to-use toggle switch that lets you turn Presentation Mode on or off
- Works on Mac and Windows computers
- Support for HD video resolutions up to 1920 x 1200
- Hassle-free connection with the reversible USB-C connector
- Maximum portability with a small footprint and lightweight design
- Thunderbolt 3 port compatible

Hardware

Warranty	3 Years
AV Input	USB-C
Ports	1
AV Output	VGA

Performance

Maximum Analog Resolutions	2048 x 1280, 1920 x 1200 @ 60hz
Supported Resolutions	1024 x 768
	1280 x 720
	1920 x 1080
	1920 x 1200
	2048 x 1280
Wide Screen Supported	Yes
Audio Specifications	VGA - No Audio Support

Connector(s)

Connector A	1 - USB-C (24 pin) DisplayPort Alt Mode
Connector B	1 - VGA (15 pin, High Density D-Sub)

Special Notes / Requirements

System and Cable Requirements	Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter.
-------------------------------	---

Environmental

Operating Temperature	5C to 35C (41F to 95F)
Storage Temperature	5C to 35C (41F to 95F)
Humidity	25% to 85% RH Non-Condensing

Physical Characteristics

Color	Black
Accent Color	Black
Cable Length	3.7 in [95 mm]
Product Length	7.3 in [18.6 cm]
Product Width	1.7 in [4.3 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	1.0 oz [29 g]

**Packaging
Information**

Package Length	9.2 in [23.3 cm]
Package Width	3.1 in [8.0 cm]
Package Height	0.8 in [2.1 cm]
Shipping (Package) Weight	2.4 oz [68.0 g]

What's in the Box

Included in Package	1 - USB-C to VGA video adapter
	1 - quick-start guide

**Warranty
Information**

Warranty	3 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

