

Travel A/V Adapter: 2-in-1 DisplayPort to HDMI or VGA

Product ID: DP2HDVGA



This DisplayPort to HDMI + VGA travel adapter lets you connect your DP enabled Ultrabook or laptop computer to any VGA or HDMI display.

Why keep several adapters when you only need one? With this single DisplayPort to VGA and HDMI adapter you can rest assured that your computer can interface with any modern boardroom or classroom display. It's the ideal plug-and-play solution for BYOD (Bring Your Own Device) applications at the office.

Plus, because the converter supports video resolutions up to 1920x1200 or 1080p, you can convert your DisplayPort video source to HDMI or VGA without sacrificing video quality.

The travel A/V adapter maximizes portability with a small footprint and lightweight design. This convenient construction ensures the adapter is as portable as your laptop, fitting easily into your laptop bag or carrying case and eliminates the need to carry more than one adapter.

With this adapter you can walk into virtually any boardroom ready to present, making a great first impression and saving you the embarrassment of having to rummage through your bag looking for the right connector. Plus, the 2-in-1 converter installs easily with no software or drivers required.

The StarTech.com DP2HDVGA is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility





Applications

- Keep the adapter with you while traveling to connect to virtually any display
- Connect your BYOD laptop/Ultrabook to an HDMI or VGA display at work
- Connect a VGA or HDMI display to your DisplayPort laptop, to use as a secondary monitor

Features

- 2-in-1 adapter lets you connect your DP computer to any HDMI or VGA display with a single adapter
- Maximize portability with a compact, lightweight adapter that you can easily carry in your laptop bag
- Supports video resolutions up to 1920x1200 or 1080p
- Plug-and-play installation
- No power adapter required

Hardware

Warranty	3 Years
AV Input	DisplayPort - 1.2
AV Output	HDMI - 1.4
	VGA
Audio	Yes

Performance

Maximum Cable Distance To Display	49.9 ft [15.2 m]
Maximum Analog Resolutions	1920x1200/1080p
Maximum Digital Resolutions	1920x1200/1080p
Wide Screen Supported	Yes

Audio Specifications HDMI - 7.1 Channel Audio

MTBF 1,097,978 hours

Connector(s)

Connector A 1 - DisplayPort (20 pin)

Connector B 1 - HDMI (19 pin)

1 - VGA (15 pin, High Density D-Sub)

Special Notes / Requirements

Note The HDMI port is a passive port.

The VGA port is an active port.

Maximum Cable Distance to Display refers to digital video. VGA distance capabilities are dependent upon the quality of your cabling

Environmental

Operating Temperature 0C to 60C (32F to 140F)

Storage Temperature -10C to 70C (14F to 158F)

Humidity 10-85% RH

Physical Characteristics

Color Black

Cable Length 5.9 in [15 cm]

Product Length 7.5 in [19.0 cm]

Product Width 2.3 in [5.8 cm]

Product Height 0.5 in [1.3 cm]

Weight of Product 1.3 oz [37.0 g]

Packaging Information

Package Quantity 1

Package Length 4.1 in [10.5 cm]

Package Width 7.9 in [20.1 cm]

Package Height 0.7 in [1.7 cm]

Shipping (Package) Weight 1.6 oz [46.0 g]

What's in the Box

Included in Package	1 - DisplayPort to HDMI / VGA Adapter
	1 - Instruction manual

Warranty Information

Warranty	3 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

