

DisplayPort to VGA Adapter - Active DP to VGA Converter - 1080p Video - DisplayPort Certified - DP/DP++ Source to VGA Monitor Cable Adapter Dongle - Latching DP Connector

Product ID: DP2VGA2



This DisplayPort to VGA adapter lets you connect your DP computer to a VGA monitor or projector. The adapter works with DisplayPort computers like your HP Elitebook Revolve 810 G3.

The DP to VGA adapter lets you connect your DisplayPort laptop or desktop computer to a VGA display. The adapter supports plug-and-play connectivity ensuring a hassle-free setup.

The DisplayPort adapter makes your DP computer fully compatible with existing VGA monitors or projectors in your home or around your office. The VGA connector features nuts that mate with the screws on standard VGA cables, to ensure your video cable won't get disconnected.

The DisplayPort to VGA converter maximizes portability with a compact, lightweight design, making it the perfect travel accessory to carry with your DisplayPort laptop, fitting easily into your laptop bag or carrying case. This ultra-portable design makes this adapter perfect for BYOD (Bring Your Own Device) applications at the office.

With support for video resolutions up to 1920x1200 or 1080p, you'll be surprised at the picture quality the adapter provides, even when connected to a legacy VGA monitor, projector or television. The adapter harnesses the video capabilities built into your DP connection to deliver every detail in stunning high-definition.

The DP2VGA2 is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Keep the adapter with you while you're traveling, to connect to VGA displays at trade shows or in hotel rooms
- Connect your BOYD laptop to a VGA office hot desk or boardroom projector
- Use your VGA monitor as a secondary display

Features

- **DISPLAYPORT TO VGA ADAPTER:** DisplayPort 1.2 (HBR2) adapter connects a VGA display/projector supporting 2048x1280, 1920x1200 & 1080p at 60Hz; EDID & DDC pass-through ensure compatibility between source & display 9" (22.5cm) cable DisplayPort Certified
- **COMPATIBILITY:** Active digital to analog converter supports DP or DP++ source w/ standard DP connector incl workstations, desktops (AMD/Nvidia), laptops, small form factor computers & docking stations
- **CONNECT TO A PRIMARY OR SECONDARY DISPLAY:** Connect a VGA monitor or projector, or add a second display to your workstation using this DP to VGA display adapter; Compact design makes it easy to travel to and from office or home
- **LATCHING DISPLAYPORT & SCREW LOCKING VGA:** Video adapter has latching DP connector to ensure a solid host connection Supports VGA screw locking cable to prevent cable from coming loose or accidental disconnection Tested w/ VGA cables up to 25ft
- **EASY TO USE:** With no software or drivers required, the DP to VGA adapter dongle works with any OS including Windows, Ubuntu and macOS; DisplayPort male to VGA female

Hardware

Warranty	3 Years
Active or Passive Adapter	Active
AV Input	DisplayPort - 1.2
AV Output	VGA
Audio	No

Performance

Wide Screen Supported	Yes
Audio Specifications	VGA - No Audio Support

Connector(s)

Connector A	1 - DisplayPort (20 pin)
Connector B	1 - VGA (15 pin, High Density D-Sub)

Environmental

Operating Temperature	0C to 45C (32F to 113F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	10%-85%RH

Physical Characteristics

Color	Black
Material	Plastic
Cable Length	8.9 in [225 mm]
Product Length	11.0 in [27.9 cm]
Product Width	1.4 in [3.5 cm]
Product Height	0.8 in [2.0 cm]
Weight of Product	1.5 oz [43.0 g]

Packaging Information

Package Quantity	1
Package Length	8.1 in [20.5 cm]
Package Width	7.7 in [19.6 cm]
Package Height	1.0 in [2.5 cm]
Shipping (Package) Weight	1.8 oz [52.0 g]

What's in the Box

Included in Package	1 - DisplayPort to VGA Converter
---------------------	----------------------------------

Warranty Information

Warranty	3 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***