

1 ft DVI-D Dual Link Cable - M/M

Product ID: DVIDDMM1



The DVIDDMM1 1ft DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 1 ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference

- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

Hardware

| | |
|-----------------------|-----------------------------|
| Warranty | Lifetime |
| Connector Plating | Nickel |
| Cable Jacket Material | PVC - Polyvinyl Chloride |
| Fire Rating | CMG Rated (General Purpose) |
| Industry Standards | DVI DDWG Standard |

Connector(s)

| | |
|-------------|--------------------|
| Connector A | 1 - DVI-D (25 pin) |
| Connector B | 1 - DVI-D (25 pin) |

Environmental

| | |
|-----------------------|--------------------------|
| Operating Temperature | 0C to 50C (32F to 122F) |
| Storage Temperature | -20 to 70C (-4F to 158F) |
| Humidity | 0 to 95% |

Physical Characteristics

| | |
|-------------------|-------------------|
| Color | Black |
| Wire Gauge | 28 AWG |
| Cable Length | 1.0 ft [0.3 m] |
| Product Length | 12.0 in [30.5 cm] |
| Product Width | 1.6 in [4.0 cm] |
| Product Height | 0.6 in [1.6 cm] |
| Weight of Product | 3.2 oz [91.5 g] |

Packaging Information

| | |
|------------------|---|
| Package Quantity | 1 |
|------------------|---|

| | |
|---------------------------|------------------|
| Package Length | 5.6 in [14.3 cm] |
| Package Width | 7.9 in [20.0 cm] |
| Package Height | 1.3 in [3.2 cm] |
| Shipping (Package) Weight | 3.8 oz [108.0 g] |

What's in the Box

| | |
|---------------------|--------------------------------------|
| Included in Package | 1 - 1 ft DVI-D Dual Link Cable - M/M |
|---------------------|--------------------------------------|

Warranty Information

| | |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

****Product appearance and specifications are subject to change without notice.***

